

# Eaton EBMBB

Catalog Number: EBMBB

Eaton Crouse-Hinds series EBMB circuit breaker enclosure, 10A through 150A, Without circuit breaker, Bolted/ground joint/gasketed cover construction, Copper-free aluminum



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EBMB circuit breaker enclosure	EBMBB
	UPC
	782274778266
Product Length/Depth	Product Height
10.25 in	26.9 in
Product Width	Product Weight
14.78 in	154 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

3R

4

7

9

12

## Product specifications

### Enclosure

Without circuit breaker

### Amperage Rating

10 A through 150 A

### Enclosure cover construction

Bolted/ground joint/gasketed

### Enclosure material

Copper-free aluminum

## Resources

### 3D models

[SP3D Design Package - EBMB Explosionproof Circuit Breakers](#)

### Catalogs

[EBMB Series Explosionproof Circuit Breakers catalog page](#)

### Certification reports

[EBMB Explosionproof Circuit Breakers UL certification](#)

[EBMB Explosionproof Circuit Breakers Canadian certification](#)

### Installation instructions

[IF 1616 - Flange Gasket Replacement Kit](#)

[IF 1150 - EBM Motor Control Series Combination Line Starters, Motor Starters, Circuit Breakers](#)

[IF 1149 - Wiring](#)

### Specifications and datasheets

[Eaton Specification Sheet - EBMBB](#)