



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **EGSU400NSEACA 400A Green Ats 1-PH Se N3R,** *Eaton Corp*

Catalog Number	EGSU400NSEACA
Manufacturer	Eaton Corp
Description	Green Automatic Transfer Switch, Load Management, CHSPT2ULTRA Surge Protection, 400A, 120/240V, Two-Pole, Nema 3R Enclosure, 50/60 HZ, Mechanically Held Switch
Weight per unit	130.0 (lbs/each)
Product Category	Disconnect Motor Switches

### **Dimensions and Weight**

Depth	10.0000
Height	40.0000
Width	25.0000

### **Descriptions**

Description	400A GREEN ATS 1-PH SE N3R,
extra long description	ETN EGSU400NSEACA 400A GREEN ATS, 1
Features	All Eaton automatic transfer switches (ATS) monitor utility and generator voltages and will automatically connect to the appropriate source of power. Eaton offers two types of automatic transfer switches to suit your personal backup power needs. A standard ATS EGSX series with load shedding capabilities and the Green ATS EGSU series that provides a truly active load management solution.
Long Description	Green Automatic Transfer Switch, Load management, CHSPT2ULTRA surge protection, 400A, 120/240V, Two-pole, NEMA 3R enclosure, 50/60 Hz, Mechanically held switch
Product Type	400A Green Ats, 1-PH, Se, N3R,
Special Features	Load management

### **Manufacturer Information**

Brand	EATON CUTLER-HAMMER
GTIN	00786685534480
Manufacturers Part Number	EGSU400NSEACA
UPC	786685534480

### **Taxonomies, Classifications, and Categories**

Category Description	TRANSFER SWITCHES
Type	Non-SE residential automatic transfer switch

### **Packaging**

Carton	1
Weight Per each	130



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs

standard

UL 1008