



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EL196 1/2" 90D Female/Male Elbow

Crouse-Hinds

Catalog Number	EL196
Manufacturer	Crouse-Hinds
Description	90° Elbow, 1/2 In Trade Size, EI Model, Angle Shape, Electro Galvanized and Aluminum Acrylic Paint, Female to Male Connection, 0.41 LB/Ea
Weight per unit	0.4100 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Male Threaded, Female Threaded
dimensions	1.2500 IN X 2.0600 IN X 2.2500 IN

Descriptions

Description	1/2" 90D FEMALE/MALE ELBOW
extra long description	CRS-H EL196 1/2 NPT IRON 90 DEG MAL
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit

Manufacturer Information

Brand	Eaton
GTIN	00782274308005
UPC	782274308005

Taxonomies, Classifications, and Categories

Category Description	RIGID ELBOWS
Type	ELBOW

Packaging

Carton	1
Package	10
Weight Per each	0.41

Uses, Certifications, and Standards

Enclosure	Class I Div 1 2 Group A B C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III
standard	UL 886, CSA C22.2