



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

411 Autumn Street
71901-0000, AR Hot Springs
Phone: 501-762-8210
Fax: 501-762-8211



E987R 6X6X4 PVC JCT Box

Abb Installation Products, Inc

| | |
|------------------|--|
| Catalog Number | E987R |
| Manufacturer | Abb Installation Products, Inc |
| Description | Molded Junction Box, Length 6 Inch X Width 6 Inch X Depth 4 Inch, Material Polycarbonate, Color Gray, Pack Of 10 |
| Weight per unit | 1.3 (lbs/each) |
| Product Category | PVC Bodies & Boxes |

Features

| | |
|-----------|---------------|
| Knockouts | true |
| Material | Polycarbonate |

Material, Color, and Finish

| | |
|-------|------|
| Color | Gray |
|-------|------|

Dimensions and Weight

| | |
|------|--------------------------------|
| Size | 6 Inches x 6 Inches x 4 Inches |
|------|--------------------------------|

Descriptions

| | |
|------------------------|--|
| Description | 6X6X4 PVC JCT BOX |
| extra long description | ABB E987R 6 X 6 X 4 IN PVC JUNCTION |
| Long Description | Molded Junction Box, Length 6 Inch x Width 6 Inch x Depth 4 Inch, Material Polycarbonate, Color Gray, Pack of 10 |
| Product Type | 6 X 6 X 4 In PVC Junction Box 10PK |
| Special Features | The first non-metallic junction box UL Listed with a NEMA 6P rating per Section 314, exception of the National Electrical Code |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Carlton |
| GTIN | 00034481066866 |
| Manufacturers Part Number | E987R |
| UPC | 034481066866 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | PVC BOXES |
| Type | Rigid Non-Metallic Conduit Junction Boxes |

Packaging

| | |
|-----------------|------|
| Carton | 10 |
| Weight Per each | 1.25 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Carlton junction box offers all the corrosion resistance and physical properties needed for direct burial applications |
| standard | UL E11461 / UL E11461 |