



FIG.	TIE SERIES	CATALOG NUMBER	MIN. TENSILE STRENGTH	MAX. BUNDLE DIAMETER	LENGTH	WIDTH	MATERIAL	MAX. TEMP. RATING
1	FO SERIES LOOP TIES	F0200-40-0	40LB (178N)	2" (50.8)	9' (228.6)	.5" (12.7)	LOW DENSITY POLYETHYLENE/NYLON	220°F (104.4°C)
		F0200-50-0	50LB (222.5N)			.75" (19.05)		
		F0350-40-0	40LB (178N)	3.5" (88.9)	13" (330.2)	.5" (12.7)		
		F0350-50-0	50LB (222.5N)			.75" (19.05)		
2	FOL SERIES BUCKLE TIES	FOL300-50-0	50LB (222.5N)	3" (76.2)	12" (304.8)	.75" (19.05)	NYLON	200°F (93.3°C)
		FOL500-50-0		5" (127)	18" (457.2)			
3	FOS SERIES STRIP TIES	FOS150-50-0	50LB (222.5N)	1.5" (38.1)	6" (152.4)	.75" (19.05)	LOW DENSITY POLYETHYLENE/NYLON	220°F (104.4°C)
		FOS320-50-0		3.2" (81.28)	12" (304.8)			
		FOS500-50-0		5" (127)	18" (457.2)			
4	FOR SERIES ROLL HOOK & LOOP	FOR180-50-0	50LB (222.5N)	VARIOUS	180" (4572)	.75" (19.05)	LOW DENSITY POLYETHYLENE/NYLON	220°F (104.4°C)

**BLACK IS STANDARD COLOR**  
**CONSULT CUSTOMER SERVICE FOR COLORS AND AVAILABILITY**

GENERAL NOTES			
1. DIMENSIONS IN PARENTHESES ( ) ARE IN METRIC UNITS.			
REVISIONS		DESCRIPTION:	
<input type="checkbox"/> SEE ERN ***** FOR APPROVAL SIGNATURES PROJECT NO: *****		<b>TY-GRIP™ FASTENER</b>	
		ORIGINAL PROJECT NO / ( ERN NO )	SHEET NO:
		FM401147 / ( 2003287 )	1 OF 1
		REV. NO:	DRAWING NO:
		—	WSD-000067