




GE
Lighting

10183 - F15T12/CW 6PK

GE garage & basement 15 watt T12 1-pack

- Ideal for utility use
- Lasts 4.1 years based on 6 hours per day usage
- 1.5 inch diameter T12 with medium bi-pin (g13) base
- 4100K cool white light appearance
- Cool white light perfect for sizable spaces
- For use in large spaces such as basements and garages
- GE garage & basement fluorescent bulbs' cool white light is perfect for illuminating sizable spaces throughout your home. Use in large open spaces in your home including finished and unfinished basements, garages and rec rooms
- 18 inches long



CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
 - Wear safety glasses and gloves when handling lamp.
 - Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.
- *Four year life based on rated life at 6 hours/day.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution

GENERAL CHARACTERISTICS

| | |
|----------------------------|---------------------------------------|
| Lamp Type | Linear Fluorescent - Straight Linear |
| Bulb | T12 |
| Base | Medium Bi-Pin (G13) |
| Rated Life | 9000.0 hrs |
| Bulb Material | Soda lime |
| Starting Temperature (MIN) | 10.0 °C |
| LEED-EB MR Credit | 9732 picograms Hg per mean lumen hour |
| Primary Application | Garage & Basement |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------------|----------|
| Initial Lumens | 760.0 |
| Mean Lumens | 685.0 |
| Nominal Initial Lumens per Watt | 50 |
| Color Temperature | 4100.0 K |
| Color Rendering Index (CRI) | 60.0 |

ELECTRICAL CHARACTERISTICS


| | |
|---|---------------|
| Wattage | 15.0 |
| Voltage | 47.0 |
| Open Circuit Voltage (rapid start) (MAX) | 210.0 V |
| Open Circuit Voltage (after preheating) Max @ Temperature | 220 V @ 10 °C |
| Open Circuit Voltage (rapid start) Min @ Temperature | 108 V @ 10 °C |
| Cathode Resistance Ratio - Rh/Rc (MIN) | 4.25 |
| Cathode Resistance Ratio - Rh/Rc (MAX) | 6.5 |
| Open Circuit Voltage (after preheating) Min @ Temperature | 157 V @ 10 °C |
| Current Crest Factor (MAX) | 1.7 |

DIMENSIONS


| | |
|--|----------------------|
| Maximum Overall Length (MOL) | 18.0000 in(457.2 mm) |
| Minimum Overall Length | 17.6700 in(448.8 mm) |
| Nominal Length | 18.000 in(457.2 mm) |
| Bulb Diameter (DIA) (MIN) | 1.410 in(35.8 mm) |
| Bulb Diameter (DIA) (MAX) | 1.590 in(40.4 mm) |
| Bulb Diameter (DIA) | 1.500 in(38.1 mm) |
| Max Base Face to Base Face (A) | 17.220 in(437.4 mm) |
| Face to End of Opposing Pin (B) (MIN) | 17.400 in(442.0 mm) |
| Face to End of Opposing Pin (B) (MAX) | 17.500 in(444.5 mm) |
| End of Base Pin to End of Opposite Pin End (C) | 17.670 in(448.8 mm) |

PRODUCT INFORMATION

| | |
|----------------------------------|----------------|
| Product Code | 10183 |
| Description | F15T12/CW 6PK |
| ANSI Code | 2010-1 |
| Standard Package | BUNDLE |
| Standard Package GTIN | 00043168101837 |
| Standard Package Quantity | 24 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 24 |
| UPC | 043168980500 |



Graphs_Lamp Mortality






GE
Lighting

10183 - F15T12/CW 6PK

GE garage & basement 15 watt T12 1-pack

- Ideal for utility use
- Lasts 4.1 years based on 6 hours per day usage
- 1.5 inch diameter T12 with medium bi-pin (g13) base
- 4100K cool white light appearance
- Cool white light perfect for sizable spaces
- For use in large spaces such as basements and garages
- GE garage & basement fluorescent bulbs' cool white light is perfect for illuminating sizable spaces throughout your home. Use in large open spaces in your home including finished and unfinished basements, garages and rec rooms
- 18 inches long



CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
 - Wear safety glasses and gloves when handling lamp.
 - Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.
- *Four year life based on rated life at 6 hours/day.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution

GENERAL CHARACTERISTICS

| | |
|----------------------------|---------------------------------------|
| Lamp Type | Linear Fluorescent - Straight |
| | Linear |
| Bulb | T12 |
| Base | Medium Bi-Pin (G13) |
| Rated Life | 9000.0 hrs |
| Bulb Material | Soda lime |
| Starting Temperature (MIN) | 10.0 °C |
| LEED-EB MR Credit | 9732 picograms Hg per mean lumen hour |
| Primary Application | Garage & Basement |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------------|----------|
| Initial Lumens | 760.0 |
| Mean Lumens | 685.0 |
| Nominal Initial Lumens per Watt | 50 |
| Color Temperature | 4100.0 K |
| Color Rendering Index (CRI) | 60.0 |

ELECTRICAL CHARACTERISTICS


| | |
|---|---------------|
| Wattage | 15.0 |
| Voltage | 47.0 |
| Open Circuit Voltage (rapid start) (MAX) | 210.0 V |
| Open Circuit Voltage (after preheating) Max @ Temperature | 220 V @ 10 °C |
| Open Circuit Voltage (rapid start) Min @ Temperature | 108 V @ 10 °C |
| Cathode Resistance Ratio - Rh/Rc (MIN) | 4.25 |
| Cathode Resistance Ratio - Rh/Rc (MAX) | 6.5 |
| Open Circuit Voltage (after preheating) Min @ Temperature | 157 V @ 10 °C |
| Current Crest Factor (MAX) | 1.7 |

DIMENSIONS

| | |
|--|----------------------|
| Maximum Overall Length (MOL) | 18.0000 in(457.2 mm) |
| Minimum Overall Length | 17.6700 in(448.8 mm) |
| Nominal Length | 18.000 in(457.2 mm) |
| Bulb Diameter (DIA) (MIN) | 1.410 in(35.8 mm) |
| Bulb Diameter (DIA) (MAX) | 1.590 in(40.4 mm) |
| Bulb Diameter (DIA) | 1.500 in(38.1 mm) |
| Max Base Face to Base Face (A) | 17.220 in(437.4 mm) |
| Face to End of Opposing Pin (B) (MIN) | 17.400 in(442.0 mm) |
| Face to End of Opposing Pin (B) (MAX) | 17.500 in(444.5 mm) |
| End of Base Pin to End of Opposite Pin End (C) | 17.670 in(448.8 mm) |

PRODUCT INFORMATION

| | |
|----------------------------------|----------------|
| Product Code | 10183 |
| Description | F15T12/CW 6PK |
| ANSI Code | 2010-1 |
| Standard Package | BUNDLE |
| Standard Package GTIN | 00043168101837 |
| Standard Package Quantity | 24 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 24 |
| UPC | 043168980500 |



Graphs_Lamp Mortality

