



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ED2200 Ed 65KA @ 240 V 2 Pole 200AS Load Terms

Eaton Corp

Catalog Number	ED2200
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame Molded Case Circuit Breaker, 200 A, Two - Pole, Fixed Thermal Magnetic Trip, Ed Breaker
Weight per unit	3.0 (lbs/each)
Product Category	2 Pole

### Features

Current Rating	200 A
dimensions	3.3800 IN X 2.7500 IN X 6.0000 IN
media	Yes
Poles	2
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	240 Vac, 125 Vdc

### Descriptions

Description	ED 65KA @ 240 V 2 POLE 200AS LOAD TERMS
extra long description	ETN ED2200 ED 65kA @240 V, 2P 200 A
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame molded case circuit breaker, 200 A, Two - pole, Fixed thermal magnetic trip, ED breaker
Product Type	Ed 65KA @240 V, 2P 200 As, Load Terminal

### Manufacturer Information

Brand	Eaton
GTIN	00786679456224
Manufacturers Part Number	ED2200
UPC	786679456224

### Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	3

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Frequency Rating	50 to 60 Hz
standard	UL Listed