

EI200 Series Electronic In-Wall Timers

The EI200 Series Decorator Electronic Auto Shut-Off Timers provide silent operation in time ranges from 5 minutes to 12 hours.

Features

- Silent operation in time ranges from 30 minutes to 12 hours
- Replaces single-pole switches in a variety of applications
- Requires neutral wire
- Available with and without HOLD feature
- Single button time selection
- Operates all load types including CFLs, LED lamps, and fans
- Models without HOLD feature meet Title 24 requirements

Not for use with sunlamps, saunas, or loads that could cause personal injury if timed incorrectly.

Ratings

Switch Type:	Single Pole
Switch Ratings:	
Resistive (heater):	15 Amp, 120 VAC, 1800 Watts
Tungsten (incandescent):	8.3 Amp, 120 VAC, 1000 Watts
Ballast (magnetic):	8 Amp, 120 VAC
Electronic Ballast:	500VA
Motor:	¼ HP, 120 VAC
Input Voltage:	120 VAC, 60 Hz
Operating Temperature:	32°F to 122°F (0°C to 50°C)
Style:	For use with decorator switch plates
Dimenisions:	2.79" H x 1.75" W x 1.44" D
Warranty:	Limited 1 year

Project: _____

Location: _____

Product Type: _____

Contact/Phone: _____

Model #: _____



Model Number	Time Range	Switch	Clock Volts AC	Max Wattage	Neutral Required	Color	Hold
EI200	5/10/15/30 Minute	Single-Pole	120	1800	Yes	Ivory	Yes
EI200W	5/10/15/30 Minute	Single-Pole	120	1800	Yes	White	Yes
EI200LA	5/10/15/30 Minute	Single-Pole	120	1800	Yes	Light Almond	Yes
EI205	5/15/30/45/60 Minute	Single-Pole	120	1800	Yes	Ivory	No
EI205W	5/15/30/45/60 Minute	Single-Pole	120	1800	Yes	White	No
EI205LA	5/15/30/45/60 Minute	Single-Pole	120	1800	Yes	Light Almond	No
EI210	10/20/30/60 Minute	Single-Pole	120	1800	Yes	Ivory	Yes
EI210W	10/20/30/60 Minute	Single-Pole	120	1800	Yes	White	Yes
EI210LA	10/20/30/60 Minute	Single-Pole	120	1800	Yes	Light Almond	Yes
EI215	15/30/60 Minute, 2/4 Hour	Single-Pole	120	1800	Yes	Ivory	No
EI215W	15/30/60 Minute, 2/4 Hour	Single-Pole	120	1800	Yes	White	No
EI215LA	15/30/60 Minute, 2/4 Hour	Single-Pole	120	1800	Yes	Light Almond	No
EI220	1/2/4/8 Hour	Single-Pole	120	1800	Yes	Ivory	Yes
EI220W	1/2/4/8 Hour	Single-Pole	120	1800	Yes	White	Yes
EI220LA	1/2/4/8 Hour	Single-Pole	120	1800	Yes	Light Almond	Yes
EI230	2/4/8/12 Hour	Single-Pole	120	1800	Yes	Ivory	Yes
EI230W	2/4/8/12 Hour	Single-Pole	120	1800	Yes	White	Yes
EI230LA	2/4/8/12 Hour	Single-Pole	120	1800	Yes	Light Almond	Yes
EI235	15/30/45/60/120 Minute	Single-Pole	120	1800	Yes	Ivory	No
EI235W	15/30/45/60/120 Minute	Single-Pole	120	1800	Yes	White	No
EI235LA	15/30/45/60/120 Minute	Single-Pole	120	1800	Yes	Light Almond	No

Specification

The timer shall be supplied with an LED and single-button operation. The timer must fit a standard wall box and accept a rectangular decorator wall plate. Timer contacts shall break current at the end of timed cycle. The timer shall be capable of single-pole operation. Various user selectable timing ranges shall be available up to 12 hours, with or without "HOLD" feature for constant ON. The timer shall be Intermatic model _____ (See Model Numbers Listed).

Diagrams



EI200 Series Electronic In-Wall Timers

The EI200 Series Decorator Electronic Auto Shut-Off Timers provide silent operation in time ranges from 5 minutes to 12 hours.

Features

- Silent operation in time ranges from 30 minutes to 12 hours
- Replaces single-pole switches in a variety of applications
- Requires neutral wire
- Available with and without HOLD feature
- Single button time selection
- Operates all load types including CFLs, LED lamps, and fans
- Models without HOLD feature meet Title 24 requirements

Not for use with sunlamps, saunas, or loads that could cause personal injury if timed incorrectly.

Ratings

Switch Type: Single Pole

Switch Ratings:

Resistive (heater): 15 Amp, 120 VAC, 1800 Watts

Tungsten (incandescent): 8.3 Amp, 120 VAC, 1000 Watts

Ballast (magnetic): 8 Amp, 120 VAC

Electronic Ballast: 500VA

Motor: ¼ HP, 120 VAC

Input Voltage: 120 VAC, 60 Hz

Operating Temperature: 32°F to 122°F (0°C to 50°C)

Style: For use with decorator switch plates

Dimensions: 2.79" H x 1.75" W x 1.44" D

Warranty: Limited 1 year

Project: _____

Location: _____

Product Type: _____

Contact/Phone: _____

Model #: _____



Model Number	Time Range	Switch	Clock Volts AC	Max Wattage	Neutral Required	Color	Hold
EI200	5/10/15/30 Minute	Single-Pole	120	1800	Yes	Ivory	Yes
EI200W	5/10/15/30 Minute	Single-Pole	120	1800	Yes	White	Yes
EI200LA	5/10/15/30 Minute	Single-Pole	120	1800	Yes	Light Almond	Yes
EI205	5/15/30/45/60 Minute	Single-Pole	120	1800	Yes	Ivory	No
EI205W	5/15/30/45/60 Minute	Single-Pole	120	1800	Yes	White	No
EI205LA	5/15/30/45/60 Minute	Single-Pole	120	1800	Yes	Light Almond	No
EI210	10/20/30/60 Minute	Single-Pole	120	1800	Yes	Ivory	Yes
EI210W	10/20/30/60 Minute	Single-Pole	120	1800	Yes	White	Yes
EI210LA	10/20/30/60 Minute	Single-Pole	120	1800	Yes	Light Almond	Yes
EI215	15/30/60 Minute, 2/4 Hour	Single-Pole	120	1800	Yes	Ivory	No
EI215W	15/30/60 Minute, 2/4 Hour	Single-Pole	120	1800	Yes	White	No
EI215LA	15/30/60 Minute, 2/4 Hour	Single-Pole	120	1800	Yes	Light Almond	No
EI220	1/2/4/8 Hour	Single-Pole	120	1800	Yes	Ivory	Yes
EI220W	1/2/4/8 Hour	Single-Pole	120	1800	Yes	White	Yes
EI220LA	1/2/4/8 Hour	Single-Pole	120	1800	Yes	Light Almond	Yes
EI230	2/4/8/12 Hour	Single-Pole	120	1800	Yes	Ivory	Yes
EI230W	2/4/8/12 Hour	Single-Pole	120	1800	Yes	White	Yes
EI230LA	2/4/8/12 Hour	Single-Pole	120	1800	Yes	Light Almond	Yes
EI235	15/30/45/60/120 Minute	Single-Pole	120	1800	Yes	Ivory	No
EI235W	15/30/45/60/120 Minute	Single-Pole	120	1800	Yes	White	No
EI235LA	15/30/45/60/120 Minute	Single-Pole	120	1800	Yes	Light Almond	No

Specification

The timer shall be supplied with an LED and single-button operation. The timer must fit a standard wall box and accept a rectangular decorator wall plate. Timer contacts shall break current at the end of timed cycle. The timer shall be capable of single-pole operation. Various user selectable timing ranges shall be available up to 12 hours, with or without "HOLD" feature for constant ON. The timer shall be Intermatic model _____ (See Model Numbers Listed).

Diagrams

