





GE
Lighting

86256 - FLE13HT2/2/827

GE Spiral® T2



GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	T2
Base	Medium Screw (E26)
Bulb Finish	Soft white
Equivalent Wattage	60.0 W
Rated Life	12000.0 hrs
Starting Temperature (MIN)	5.0 °C
Total Harmonic Distortion (THD)	120.0 %
LEED-EB MR Credit	600 picograms Hg per mean lumen hour
Primary Application	Standard

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	870.0
Mean Lumens	695.0
Nominal Initial Lumens per Watt	66
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

ELECTRICAL CHARACTERISTICS

Wattage	13.0
Input Voltage	120.0 V
Input Current	0.1900 A
Power Factor	0.5

DIMENSIONS

Maximum Overall Length (MOL)	3.9000 in(99.1 mm)
Nominal Length	3.900 in(99.1 mm)

PRODUCT INFORMATION

Product Code	86256
Description	FLE13HT2/2/827
Standard Package	Case
Standard Package GTIN	10043168862568
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168862561

NOTES



- Best performance if operated base up and at 77 degrees F (25C) ambient temperature.
- Fluorescent lamp lumens decline during life
- Lumens on one piece self ballasted lamp systems are measured base up.
- Most one piece self ballasted lamps for incandescent sockets and plug-in lamps with screw-in adapters do not work with clip-on shades
- Use only on 120V 60 Hz circuits. Do not use on dimming circuits, photocells or timers. Do not use in wet locations.



GE
Lighting

86256 - FLE13HT2/2/827

GE Spiral® T2



GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	T2
Base	Medium Screw (E26)
Bulb Finish	Soft white
Equivalent Wattage	60.0 W
Rated Life	12000.0 hrs
Starting Temperature (MIN)	5.0 °C
Total Harmonic Distortion (THD)	120.0 %
LEED-EB MR Credit	600 picograms Hg per mean lumen hour
Primary Application	Standard

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	870.0
Mean Lumens	695.0
Nominal Initial Lumens per Watt	66
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

ELECTRICAL CHARACTERISTICS

Wattage	13.0
Input Voltage	120.0 V
Input Current	0.1900 A
Power Factor	0.5

DIMENSIONS

Maximum Overall Length (MOL)	3.9000 in(99.1 mm)
Nominal Length	3.900 in(99.1 mm)

PRODUCT INFORMATION

Product Code	86256
Description	FLE13HT2/2/827
Standard Package	Case
Standard Package GTIN	10043168862568
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168862561

NOTES

- Best performance if operated base up and at 77 degrees F (25C) ambient temperature.
- Fluorescent lamp lumens decline during life
- Lumens on one piece self ballasted lamp systems are measured base up.
- Most one piece self ballasted lamps for incandescent sockets and plug-in lamps with screw-in adapters do not work with clip-on shades
- Use only on 120V 60 Hz circuits. Do not use on dimming circuits, photocells or timers. Do not use in wet locations.