

# EVLP Low Profile Hazard•Gard® (H.I.D.) Luminaires

## Medium and Mogul Base

Cl. I, Div. 1, Groups B (GB suffix), C, D  
 Cl. I, Zone 1, Groups IIB + H<sub>2</sub> (with suffix – GB), IIB, IIA  
 Cl. II, Div. 1, Groups E, F, G; Class III

Marine & Wet Locations  
 3, 3R, 4, 4X; IP66

**4L**

### Applications:

- Eaton's Crouse-Hinds Low Profile Hazard•Gard® luminaires are used in:
- Areas where flammable or explosive vapors or gases are present
  - Hazardous areas, both indoors and outdoors, where long life and low maintenance costs are desired
  - Petroleum refineries, chemical, petrochemical and pharmaceutical plants, oil terminals, gas plants and other heavy process industry facilities
  - Waste treatment facilities
  - Drilling platforms and other coastal and offshore hazardous areas



### Features and Benefits:

- Small, compact size is perfect where low mounting restrictions are a concern.
- Two start Acme threaded construction allows for easier assembly, installation and maintenance.
- Lightweight copper-free aluminum housing with powdered epoxy finish for superior corrosion resistance.
- All exterior hardware is corrosion-resistant stainless steel.
- Four mounting arrangements: pendant, ceiling, wall bracket and stanchion suit any lighting layout.
- Wide range of light sources and wattages to meet specific lighting needs.
- Marine and NEMA 4X construction suitable for outdoor, hose down, marine and corrosive environments.
- Integral ballast for lowest installed cost.
- High power factor (90%+) ballasts allows more fixtures per circuit.
- Uses same mounting modules as the standard Hazard•Gard® for easy retrofitting when the EVLP is the preferred choice.
- Internally fluted glass globe reduces glare and distributes light evenly – ideal for adverse environments typical of industrial facilities.
- Krydon® construction dome and angle reflectors – won't rust, corrode, dent, chip or peel
- Now available in components – luminaire body, mounting module, guard, reflectors – allowing for easy stocking for Quick Ship requirements.

### Certifications and Compliances:

- NEC and CEC:
  - Class I, Division 1, Groups B (with suffix GB), C, D – All Wattages
  - Class I, Zone 1, Groups IIB + H<sub>2</sub> (with suffix GB), IIB, IIA – All Wattages
  - Class II and Class III
- UL Standards:
  - 844, Hazardous (Classified) Locations
  - 1598 Luminaires
  - 1598A Marine Locations
- CSA Standards
  - C22.2 No. 137

### Options:

Description	Suffix
• Group B suitability .....	<b>GB</b>
• Ballast-Gard™ (HPS only) .....	<b>BG</b>
• Instant restrike (Mogul Base only) .....	<b>IR</b>
70–150W LX HPS	
• Cannot use with BG Option	
• Fused (not suitable for marine applications).....	<b>S658*</b>
• Quartz auxiliary lighting (Mogul Base only) .....	<b>QTZ</b>
• Cannot use with IR option	
• Uses 100W single ended double contract lamp	
• Quartz lamp not included	
• Factory assembled with lamps .....	<b>FA</b>

\*When ordering fuses for luminaires, option S658, you must specify the operating voltage. S658 cannot be ordered with /MT in the catalog number.

### Accessories:

Description	Cat. #
Dome reflector	<b>RD739</b>
Angle reflector	<b>RA739</b>

### Standard Materials:

- Mounting modules, cover, ballast housing, globe holder – copper-free aluminum
- Globe – heat and impact resistant glass
- Exterior hardware – stainless steel
- Reflectors (dome & angle) – Krydon® fiberglass-reinforced polyester

### Standard Finishes:

- Copper-free aluminum – Corro-free™ powdered epoxy
- Krydon – white
- Stainless steel guard

### Ratings (Electrical/Size):

#### Sources/Wattage:

- Medium Base 70–150W HPS, 70–175W MH
- Mogul Base 70–150W HPS, 70–250W MH

#### Voltages:

- Medium & Mogul H.I.D.
  - 120V 60Hz
  - Multi-tap (120, 208, 240, 277V 60Hz)
  - Tri-tap (120, 277, 347V 60Hz)
  - 480V 60Hz
  - Other voltages – consult Eaton's Crouse-Hinds

#### Conduit Entries:

- ¾", 1" NPT – pendant, wall bracket, ceiling
- 1¼" NPT – stanchion

**4L**


# 4L EVLP Low Profile Hazard•Gard®

Medium Base


Cl. I, Div. 1, Groups B (GB suffix), C, D  
 Cl. I, Zone 1, Groups IIB + H<sub>2</sub> (with GB suffix), IIB, IIA  
 Cl. II, Div. 1, Groups E, F, G; Class III

Marine & Wet Locations  
 3, 3R, 4, 4X; IP66


## Ordering Information:




Pendant Mount



†Wall Bracket Mount



†Ceiling Mount



Stanchion Mount

	Pendant		Wall Bracket		Ceiling		Stanchion		Luminaire Body Less Mounting Module & Guard
	Hub Watt	With Guard Size (In.) Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #		Cat. #
<b>High Pressure Sodium</b>									
70W	3/4	EVLPA142071	EVLPBX142071	EVLPCX142071					EVLPA14070
	1	EVLPA143071	EVLPBX143071	EVLPCX143071					
	1 1/4						EVLPA144071		
100W	3/4	EVLPA142101	EVLPBX142101	EVLPCX142101					EVLPA14100
	1	EVLPA143101	EVLPBX143101	EVLPCX143101					
	1 1/4						EVLPA144101		
150W	3/4	EVLPA142151	EVLPBX142151	EVLPCX142151					EVLPA14151
	1	EVLPA143151	EVLPBX143151	EVLPCX143151					
	1 1/4						EVLPA144151		
<b>Pulse Start Metal Halide</b>									
150W	3/4	EVLPA192151 S828	EVLPBX192151 S828	EVLPCX192151 S828					EVLPA19150 S828
	1	EVLPA193151 S828	EVLPBX193151 S828	EVLPCX193151 S828					
	1 1/4						EVLPA194151 S828		
175W	3/4	EVLPA192171 S828	EVLPBX192171 S828	EVLPCX192171 S828					EVLPA19175 S828
	1	EVLPA193171 S828	EVLPBX193171 S828	EVLPCX193171 S828					
	1 1/4						EVLPA194171 S828		
<b>Metal Halide</b>									
70W	3/4	EVLPA192071	EVLPBX192071	EVLPCX192071					EVLPA19070
	1	EVLPA193071	EVLPBX193071	EVLPCX193071					
	1 1/4						EVLPA194071		
100W	3/4	EVLPA192101	EVLPBX192101	EVLPCX192101					EVLPA19100
	1	EVLPA193101	EVLPBX193101	EVLPCX193101					
	1 1/4						EVLPA194101		
175W	3/4	EVLPA192171	EVLPBX192171	EVLPCX192171					EVLPA19175
	1	EVLPA193171	EVLPBX193171	EVLPCX193171					
	1 1/4						EVLPA194171		

### Complete Catalog Number as follows:

Standard Voltage Ballasts – 60Hz

Voltage Suffix	Multi Tap /MT	NEC/UL		CEC/CSA (cUL)	
		120V /120	480V /480	Tri Tap /TT	120V /120

Optional Voltage Ballasts – 50 or 60Hz

Voltage Suffix	*CEC/CSA (cUL)– CWI Isolated Ballasts			EXPORT			
	208V CWI /208CWI	240V CWI /240CWI	600V CWI /600CWI	220V 60Hz /220	220V 50Hz /220 50	230V 50Hz /230 50	240V 50Hz /240 50

2. 150W HPS Luminaires only

- 55V lamps – add suffix "LX"
- 100V lamps – add suffix "CE"

†Ceiling and bracket mounts have 4 hubs: 3 are plugged.

\*CWI Isolated Ballasts are only available for high pressure sodium and 175W metal halide (non pulse start) luminaires.

# EVLP Low Profile Hazard•Gard®


## Mogul Base

Cl. I, Div. 1, Groups B (GB suffix), C, D  
 Cl. I, Zone 1, Groups IIB + H<sub>2</sub>  
 (with GB suffix), IIB, IIA  
 Cl. II, Div. 1, Groups E, F, G; Class III


Marine & Wet Locations  
 3, 3R, 4, 4X; IP66

**4L**


### Ordering Information:




Pendant Mount



†Wall Bracket Mount



†Ceiling Mount



Stanchion Mount

Watt Size (In.)	Pendant		Wall Bracket		Ceiling		Stanchion		Luminaire Body Less Mounting Module & Guard Cat. #
	Hub	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #		
<b>High Pressure Sodium</b>									
70W	3/4	EVLP042071	EVLPBX042071	EVLPBX042071	EVLP042071	EVLP042071			EVLP04070
	1	EVLP043071	EVLPBX043071	EVLPBX043071	EVLP043071	EVLP043071			
	1 1/4						EVLPJ044071		
100W	3/4	EVLP042101	EVLPBX042101	EVLPBX042101	EVLP042101	EVLP042101			EVLP04100
	1	EVLP043101	EVLPBX043101	EVLPBX043101	EVLP043101	EVLP043101			
	1 1/4						EVLPJ044101		
150W	3/4	EVLP042151	EVLPBX042151	EVLPBX042151	EVLP042151	EVLP042151			EVLP04150
	1	EVLP043151	EVLPBX043151	EVLPBX043151	EVLP043151	EVLP043151			
	1 1/4						EVLPJ044151		
<b>Pulse Start Metal Halide</b>									
150W	3/4	EVLP092151S828	EVLPBX092151S828	EVLPBX092151S828	EVLP092151S828	EVLP092151S828			EVLP09150S828
	1	EVLP093151S828	EVLPBX093151S828	EVLPBX093151S828	EVLP093151S828	EVLP093151S828			
	1 1/4						EVLPJ094151S828		
175W	3/4	EVLP092171S828	EVLPBX092171S828	EVLPBX092171S828	EVLP092171S828	EVLP092171S828			EVLP09170S828
	1	EVLP093171S828	EVLPBX093171S828	EVLPBX093171S828	EVLP093171S828	EVLP093171S828			
	1 1/4						EVLPJ094171S828		
200W	3/4	EVLP092201S828	EVLPBX092201S828	EVLPBX092201S828	EVLP092201S828	EVLP092201S828			EVLP09201S828
	1	EVLP093201S828	EVLPBX093201S828	EVLPBX093201S828	EVLP093201S828	EVLP093201S828			
	1 1/4						EVLPJ094201S828		
250W	3/4	EVLP092251S828	EVLPBX092251S828	EVLPBX092251S828	EVLP092251S828	EVLP092251S828			EVLP09250S828
	1	EVLP093251S828	EVLPBX093251S828	EVLPBX093251S828	EVLP093251S828	EVLP093251S828			
	1 1/4						EVLPJ094251S828		
<b>Metal Halide</b>									
70W	3/4	EVLP092071	EVLPBX092071	EVLPBX092071	EVLP092071	EVLP092071			EVLP09070
	1	EVLP093071	EVLPBX093071	EVLPBX093071	EVLP093071	EVLP093071			
	1 1/4						EVLPJ094071		
100W	3/4	EVLP092101	EVLPBX092101	EVLPBX092101	EVLP092101	EVLP092101			EVLP09100
	1	EVLP093101	EVLPBX093101	EVLPBX093101	EVLP093101	EVLP093101			
	1 1/4						EVLPJ094101		
175W	3/4	EVLP092171	EVLPBX092171	EVLPBX092171	EVLP092171	EVLP092171			EVLP09170
	1	EVLP093171	EVLPBX093171	EVLPBX093171	EVLP093171	EVLP093171			
	1 1/4						EVLPJ094171		
250W	3/4	EVLP092251	EVLPBX092251	EVLPBX092251	EVLP092251	EVLP092251			EVLP09250
	1	EVLP093251	EVLPBX093251	EVLPBX093251	EVLP093251	EVLP093251			
	1 1/4						EVLPJ094251		

### Complete Catalog Number as follows:

Standard Voltage Ballasts – 60Hz									
1. NEC/UL									
Voltage Suffix	Multi Tap /MT	120V		480V		CEC/CSA (cUL)		120V	
		/120	/480	Tri Tap /TT	/120	/120			
Optional Voltage Ballasts – 50 or 60Hz									
*CEC/CSA (cUL)– CWI Isolated Ballasts									
Voltage Suffix	*CEC/CSA (cUL)– CWI Isolated Ballasts			EXPORT					
	208V CWI /208CWI	240V CWI /240CWI	600V CWI /600CWI	220V 60Hz /220	220V 50Hz /220 50	230V 50Hz /230 50	240V 50Hz /240 50		

2. 150W HPS Luminaires only
- 55V lamps – add suffix "LX"
  - 100V lamps – add suffix "CE"
- Example: EVLP043151/MT-LX

†Ceiling and wall bracket mounts have 4 hubs; 3 are plugged.

\*CWI Isolated Ballasts are only available for high pressure sodium and 175W–250W metal halide (non pulse start) luminaires.

# 4L EVLP Low Profile Hazard•Gard®

## Ordering by Components


**EVLP Luminaires are available in components.**

A complete luminaire consists of:

- Mounting Module
- Luminaire Body
- Guard, Dome Reflector or Angle Reflector

### Mounting Modules:

Type	Conduit	Cat. #
Pendant	3/4"	EVMP2
	1"	EVMP3
Ceiling & Wall Box	3/4"	EV22
	1"	EV33
Wall Bracket Arm	Use EV22 or EV33 box with EV87	EV87
Stanchion	1 1/4"	EVMJ4
<b>Guards</b>		
Medium		EV511
Mogul		EV512
<b>Reflectors</b>		
Dome		RD739
Angle		RA739



4L

**Medium Base Lamp Luminaires:**

Maximum Ambient	Watts	Class I, Group B (w/GB suffix) Groups C, D			Class II, Groups E, F, G Class III Simultaneous Presence		Supply Wire °C
		40°C	55°C	65°C	40°C		
High Pressure Sodium	70W	T5	T4A	T4A	T4A		90°C
	100W	T4A	T4A	T4	T4		90°C
	150W	T4	T3C	—	—		90°C
Metal Halide (including pulse start)	70W	T5	T4A	T4A	T4		85°C
	100W	T3C	T3C	—	—		90°C
	150W	T3C	T3B	—	—		90°C
	175W	T3C	T3B	—	—		90°C

**Mogul Base Lamp Luminaires:**

Maximum Ambient	Watts	Class I, Group B (w/GB suffix) Groups C, D			Class II, Groups E, F, G Class III Simultaneous Presence		Supply Wire °C
		40°C	55°C	65°C	40°C		
High Pressure Sodium	70W	T6	T5	T5	T5		90°C
	100W	T5	T4A	—	T4A		90°C
	150W	T4A	T4	—	T4		90°C
Metal Halide (including pulse start)	70W	T6	T5	T5	T5		85°C
	100W	T5	T4A	T4A	T4A		90°C
	150W	T4	T3C	—	T3C		90°C
	175W	T4	T3C	—	T3C		90°C
	200W	T3C	—	—	—		90°C
	250W	T3C	—	—	—		90°C




# 4L EVLP Low Profile Hazard•Gard®

## Dimensions and Weights

### Dimensions In Inches:

	A	B	C	D	E	F
Medium Base	13.92	12.73	16.50	16.71	20.59	19.36
Mogul Base	15.69	14.69	18.25	18.46	22.34	21.30



### 4L Weights (lbs.):


Source	Watts	Luminaire w/guard	
		Medium	Mogul
High Pressure Sodium	70	34	36.5
	100	36	38.5
	150	36.5	39
Metal Halide	70	33.5	36
	100	34.5	37
	150	36	38.5
	175	36	38.5
	200	—	40.5
	250	—	40.5
<b>Add Mounting Modules:</b>		<b>Medium</b>	<b>Mogul</b>
Pendant		1	1
Ceiling		2	2
Bracket		4.5	4.5
Stanchion		2.5	2.5
<b>Add For Reflectors:</b>			
RA739		1	1
RD739		1	1
<b>Deduct for Wire Guard</b>		0.5	0.5

**Medium Base**

**Medium Base**

**Luminaire with Globe and Guard**


**EVLP143151 Lamp: 150W/B17 High Pressure Sodium (HPS)**



**Medium Base**

**Luminaire with Globe and Dome Reflector (Less Guard)**

**EVLP143150RD Lamp: 150W/B17 High Pressure Sodium (HPS)**



4L

# EVLP Low Profile Hazard•Gard®


Photometric Data

Medium and Mogul Base

## Medium Base

### Luminaire with Globe and 30° Angle Reflector (Less Guard)


EVLP143150RA Lamp: 150W/B17 High Pressure Sodium (HPS)



## Mogul Base

### Luminaire with Globe and Guard

EVLP14043151 Lamp: 150W/E23-1/2 High Pressure Sodium (HPS)



4L




**Mogul Base**

**Mogul Base**

**Luminaire with Globe and Dome Reflector (Less Guard)**


**EVLP043150RD Lamp: 150W/E23-1/2 High Pressure Sodium (HPS)**



**Mogul Base**

**Luminaire with Globe and 30° Angle Reflector (Less Guard)**

**EVLP043150RA Lamp: 150W/E23-1/2 High Pressure Sodium (HPS)**



4L

# EVLP Low Profile Hazard•Gard®


## Mogul Base

Photometric Data

### Mogul Base

Luminaire with Globe and Guard

EVLP093171 Lamp: 175W/ED28 Metal Halide (MH)



CANDELAS		ZONAL LUMENS	
Mid-Zone Angle	Candelas	Zone	Lumens
0	2439	0-10	158
5	1750	10-20	313
15	1089	20-30	464
25	1017	30-40	563
35	915	40-50	732
45	917	50-60	922
55	1035	60-70	1128
65	1229	70-80	1377
75	1337	80-90	1473
85	1359	90-100	1452
95	1335	100-110	1257
105	1196	110-120	427
115	390	120-130	23
125	24	130-140	9
135	12	140-150	3
145	9	150-160	0
155	0	160-170	0
165	0	170-180	0
175	0		
180	0		

**\*Note:** Photometric data was developed using a 175 watt clear metal halide lamp (14,000 lumens). For other clear lamp wattages, use the following conversion factors (multipliers) with both candlepower distribution and isofotocandle charts. Multipliers do not apply to coefficients of utilization.

LAMP WATTS	CONVERSION FACTOR
70 W (MH)	0.40
100 W (MH)	0.56
250 W (MH)	1.46

LUMINAIRE SPACING RATIO – 0.4 (Spacing to mounting height ratio)  
(For additional photometric data, contact Crouse-Hinds)

**COEFFICIENTS OF UTILIZATION**  
Effective Floor Cavity Reflectance 20%

**ROOM CAVITY RATIO**

Eff. Ceil. Wall	0	1	2	3	4	5	6	7	8	9	10	
80°	70	82	70	62	56	51	46	43	39	36	34	31
70°	30	61	44	35	28	24	21	18	16	14	13	11
50°	10	82	56	42	33	28	23	19	17	14	13	11
30°	70	78	66	58	52	47	43	40	36	34	31	29
10°	50	78	61	51	44	38	34	30	27	24	22	20
0°	30	78	57	45	37	31	27	23	20	18	16	14
0°	10	78	53	40	32	26	22	18	16	14	12	11
80°	50	69	54	45	38	33	29	26	23	21	19	18
70°	30	69	50	40	33	28	24	21	18	16	14	13
50°	10	69	47	36	28	23	19	16	14	12	11	10
30°	50	61	47	39	33	29	26	23	20	19	17	16
10°	30	61	44	35	28	24	21	18	16	14	13	11
0°	10	61	42	31	25	21	17	15	12	11	10	9
80°	50	54	41	33	28	25	22	20	18	16	15	14
70°	30	54	39	30	25	21	18	16	14	12	11	10
50°	10	54	37	27	22	18	15	13	11	10	8	7
30°	0	51	33	24	19	15	13	11	9	8	7	6
10°	0	51	33	24	19	15	13	11	9	8	7	6

**ISOFOOTCANDLE CHART:**  
Footcandle Values for Isofootcandle Lines


Mtg. Hgt.	A	B	C	D	E	F
10'	20.00	10.00	5.00	2.00	1.00	0.50
12'	13.88	6.94	3.47	1.39	0.69	0.35
16'	7.82	3.91	1.96	0.78	0.39	0.20
20'	5.00	2.50	1.25	0.50	0.25	0.13
25'	3.20	1.60	0.80	0.32	0.16	0.08

**\*Percent Reflectance**

### Mogul Base

Luminaire with Globe and Dome Reflector (Less Guard)

EVLP093170RD Lamp: 175W/ED28 Metal Halide (MH)



CANDELAS		ZONAL LUMENS	
Mid-Zone Angle	Candelas	Zone	Lumens
0	3941	0-10	300
5	3241	10-20	763
15	2651	20-30	1249
25	2777	30-40	1399
35	2219	40-50	1594
45	2047	50-60	1671
55	1880	60-70	1466
65	1693	70-80	466
75	432	80-90	121
85	102	90-100	20
95	14	100-110	88
105	99	110-120	16
115	13	120-130	2
125	3	130-140	0
135	0	140-150	0
145	0	150-160	0
155	0	160-170	0
165	0	170-180	0
175	0		
180	0		

**\*Note:** Photometric data was developed using a 175 watt clear metal halide lamp (14,000 lumens). For other clear lamp wattages, use the following conversion factors (multipliers) with both candlepower distribution and isofotocandle charts. Multipliers do not apply to coefficients of utilization.

LAMP WATTS	CONVERSION FACTOR
70 W (MH)	0.40
100 W (MH)	0.56
250 W (MH)	1.46

LUMINAIRE SPACING RATIO – 1.0 (Spacing to mounting height ratio)

**COEFFICIENTS OF UTILIZATION**  
Effective Floor Cavity Reflectance 20%

**ROOM CAVITY RATIO**

Eff. Ceil. Wall	0	1	2	3	4	5	6	7	8	9	10	
80°	70	78	71	65	60	55	50	46	42	39	36	34
70°	30	78	66	56	48	42	36	31	27	24	22	20
50°	10	78	64	53	44	37	32	27	23	21	18	16
30°	70	76	70	64	58	53	49	45	41	38	35	33
10°	50	76	67	59	52	46	41	37	33	30	27	24
0°	30	76	65	55	47	41	36	31	27	24	22	19
0°	10	76	62	52	44	37	32	27	23	20	18	16
80°	50	72	64	57	50	45	40	35	31	29	26	24
70°	30	72	62	53	46	40	35	30	27	24	21	19
50°	10	72	60	51	43	37	31	27	23	20	18	16
30°	50	69	61	54	48	43	38	34	30	28	25	23
10°	30	69	60	52	45	39	34	30	26	23	21	19
0°	10	69	58	49	42	36	31	26	23	20	18	16
80°	50	66	58	52	46	41	37	33	30	27	24	22
70°	30	66	58	50	43	38	33	29	26	23	20	18
50°	10	66	56	48	41	35	30	26	23	20	18	16
30°	0	65	55	47	40	34	29	25	21	19	16	14
10°	0	65	55	47	40	34	29	25	21	19	16	14

**ISOFOOTCANDLE CHART:**  
Footcandle Values for Isofootcandle Lines

Mtg. Hgt.	A	B	C	D	E	F
10'	20.00	10.00	5.00	2.00	1.00	0.50
12'	13.88	6.94	3.47	1.39	0.69	0.35
16'	7.82	3.91	1.96	0.78	0.39	0.20
20'	5.00	2.50	1.25	0.50	0.25	0.13
25'	3.20	1.60	0.80	0.32	0.16	0.08


**\*Percent Reflectance**

**Mogul Base**

**Mogul Base**

**Luminaire with Globe and 30° Angle Reflector (Less Guard)**

**EVLPA093170RA Lamp: 175W/ED28 Metal Halide (MH)**



# EVLP Low Profile Hazard•Gard® (H.I.D.) Luminaires

## Medium and Mogul Base

Cl. I, Div. 1, Groups B (GB suffix), C, D  
 Cl. I, Zone 1, Groups IIB + H<sub>2</sub> (with suffix – GB), IIB, IIA  
 Cl. II, Div. 1, Groups E, F, G; Class III

Marine & Wet Locations  
 3, 3R, 4, 4X; IP66

**4L**

### Applications:

- Eaton's Crouse-Hinds Low Profile Hazard•Gard® luminaires are used in:
- Areas where flammable or explosive vapors or gases are present
  - Hazardous areas, both indoors and outdoors, where long life and low maintenance costs are desired
  - Petroleum refineries, chemical, petrochemical and pharmaceutical plants, oil terminals, gas plants and other heavy process industry facilities
  - Waste treatment facilities
  - Drilling platforms and other coastal and offshore hazardous areas



### Features and Benefits:

- Small, compact size is perfect where low mounting restrictions are a concern.
- Two start Acme threaded construction allows for easier assembly, installation and maintenance.
- Lightweight copper-free aluminum housing with powdered epoxy finish for superior corrosion resistance.
- All exterior hardware is corrosion-resistant stainless steel.
- Four mounting arrangements: pendant, ceiling, wall bracket and stanchion suit any lighting layout.
- Wide range of light sources and wattages to meet specific lighting needs.
- Marine and NEMA 4X construction suitable for outdoor, hose down, marine and corrosive environments.
- Integral ballast for lowest installed cost.
- High power factor (90%+) ballasts allows more fixtures per circuit.
- Uses same mounting modules as the standard Hazard•Gard® for easy retrofitting when the EVLP is the preferred choice.
- Internally fluted glass globe reduces glare and distributes light evenly – ideal for adverse environments typical of industrial facilities.
- Krydon® construction dome and angle reflectors – won't rust, corrode, dent, chip or peel
- Now available in components – luminaire body, mounting module, guard, reflectors – allowing for easy stocking for Quick Ship requirements.

### Certifications and Compliances:

- NEC and CEC:
  - Class I, Division 1, Groups B (with suffix GB), C, D – All Wattages
  - Class I, Zone 1, Groups IIB + H<sub>2</sub> (with suffix GB), IIB, IIA – All Wattages
  - Class II and Class III
- UL Standards:
  - 844, Hazardous (Classified) Locations
  - 1598 Luminaires
  - 1598A Marine Locations
- CSA Standards
  - C22.2 No. 137

### Options:

Description	Suffix
• Group B suitability .....	<b>GB</b>
• Ballast-Gard™ (HPS only) .....	<b>BG</b>
• Instant restrike (Mogul Base only) .....	<b>IR</b>
70–150W LX HPS	
• Cannot use with BG Option	
• Fused (not suitable for marine applications).....	<b>S658*</b>
• Quartz auxiliary lighting (Mogul Base only) .....	<b>QTZ</b>
• Cannot use with IR option	
• Uses 100W single ended double contract lamp	
• Quartz lamp not included	
• Factory assembled with lamps .....	<b>FA</b>

\*When ordering fuses for luminaires, option S658, you must specify the operating voltage. S658 cannot be ordered with /MT in the catalog number.

### Accessories:

Description	Cat. #
Dome reflector	<b>RD739</b>
Angle reflector	<b>RA739</b>

### Standard Materials:

- Mounting modules, cover, ballast housing, globe holder – copper-free aluminum
- Globe – heat and impact resistant glass
- Exterior hardware – stainless steel
- Reflectors (dome & angle) – Krydon® fiberglass-reinforced polyester

### Standard Finishes:

- Copper-free aluminum – Corro-free™ powdered epoxy
- Krydon – white
- Stainless steel guard

### Ratings (Electrical/Size):

#### Sources/Wattage:

- Medium Base 70–150W HPS, 70–175W MH
- Mogul Base 70–150W HPS, 70–250W MH

#### Voltages:

- Medium & Mogul H.I.D.
  - 120V 60Hz
  - Multi-tap (120, 208, 240, 277V 60Hz)
  - Tri-tap (120, 277, 347V 60Hz)
  - 480V 60Hz
  - Other voltages – consult Eaton's Crouse-Hinds

#### Conduit Entries:

- ¾", 1" NPT – pendant, wall bracket, ceiling
- 1¼" NPT – stanchion

**4L**


# 4L EVLP Low Profile Hazard•Gard®

Medium Base


Cl. I, Div. 1, Groups B (GB suffix), C, D  
 Cl. I, Zone 1, Groups IIB + H<sub>2</sub> (with GB suffix), IIB, IIA  
 Cl. II, Div. 1, Groups E, F, G; Class III

Marine & Wet Locations  
 3, 3R, 4, 4X; IP66


## Ordering Information:




Pendant Mount



†Wall Bracket Mount



†Ceiling Mount



Stanchion Mount

	Pendant		Wall Bracket		Ceiling		Stanchion		Luminaire Body Less Mounting Module & Guard
	Hub Watt	With Guard Size (In.) Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #		Cat. #
<b>High Pressure Sodium</b>									
70W	3/4	EVLPA142071	EVLPBX142071	EVLPCX142071					EVLPA14070
	1	EVLPA143071	EVLPBX143071	EVLPCX143071					
	1 1/4						EVLPA144071		
100W	3/4	EVLPA142101	EVLPBX142101	EVLPCX142101					EVLPA14100
	1	EVLPA143101	EVLPBX143101	EVLPCX143101					
	1 1/4						EVLPA144101		
150W	3/4	EVLPA142151	EVLPBX142151	EVLPCX142151					EVLPA14151
	1	EVLPA143151	EVLPBX143151	EVLPCX143151					
	1 1/4						EVLPA144151		
<b>Pulse Start Metal Halide</b>									
150W	3/4	EVLPA192151 S828	EVLPBX192151 S828	EVLPCX192151 S828					EVLPA19150 S828
	1	EVLPA193151 S828	EVLPBX193151 S828	EVLPCX193151 S828					
	1 1/4						EVLPA194151 S828		
175W	3/4	EVLPA192171 S828	EVLPBX192171 S828	EVLPCX192171 S828					EVLPA19175 S828
	1	EVLPA193171 S828	EVLPBX193171 S828	EVLPCX193171 S828					
	1 1/4						EVLPA194171 S828		
<b>Metal Halide</b>									
70W	3/4	EVLPA192071	EVLPBX192071	EVLPCX192071					EVLPA19070
	1	EVLPA193071	EVLPBX193071	EVLPCX193071					
	1 1/4						EVLPA194071		
100W	3/4	EVLPA192101	EVLPBX192101	EVLPCX192101					EVLPA19100
	1	EVLPA193101	EVLPBX193101	EVLPCX193101					
	1 1/4						EVLPA194101		
175W	3/4	EVLPA192171	EVLPBX192171	EVLPCX192171					EVLPA19175
	1	EVLPA193171	EVLPBX193171	EVLPCX193171					
	1 1/4						EVLPA194171		

### Complete Catalog Number as follows:

Standard Voltage Ballasts – 60Hz					
NEC/UL			CEC/CSA (cUL)		
Voltage Suffix	Multi Tap /MT	120V /120	480V /480	Tri Tap /TT	120V /120
Optional Voltage Ballasts – 50 or 60Hz					
*CEC/CSA (cUL)– CWI Isolated Ballasts				EXPORT	
Voltage Suffix	208V CWI /208CWI	240V CWI /240CWI	600V CWI /600CWI	220V 60Hz /220	220V 50Hz /220 50
				230V 50Hz /230 50	240V 50Hz /240 50

2. 150W HPS Luminaires only

- 55V lamps – add suffix "LX"
- 100V lamps – add suffix "CE"

†Ceiling and bracket mounts have 4 hubs: 3 are plugged.

\*CWI Isolated Ballasts are only available for high pressure sodium and 175W metal halide (non pulse start) luminaires.

# EVLP Low Profile Hazard•Gard®


## Mogul Base

Cl. I, Div. 1, Groups B (GB suffix), C, D  
 Cl. I, Zone 1, Groups IIB + H<sub>2</sub>  
 (with GB suffix), IIB, IIA  
 Cl. II, Div. 1, Groups E, F, G; Class III


Marine & Wet Locations  
 3, 3R, 4, 4X; IP66

**4L**


### Ordering Information:




Pendant Mount



†Wall Bracket Mount



†Ceiling Mount



Stanchion Mount

Watt Size (In.)	Pendant		Wall Bracket		Ceiling		Stanchion		Luminaire Body Less Mounting Module & Guard Cat. #
	Hub	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #	With Guard Cat. #		
<b>High Pressure Sodium</b>									
70W	3/4	EVLP042071	EVLPBX042071	EVLPBX042071	EVLP042071	EVLP042071			EVLP04070
	1	EVLP043071	EVLPBX043071	EVLPBX043071	EVLP043071	EVLP043071			
	1 1/4						EVLPJ044071		
100W	3/4	EVLP042101	EVLPBX042101	EVLPBX042101	EVLP042101	EVLP042101			EVLP04100
	1	EVLP043101	EVLPBX043101	EVLPBX043101	EVLP043101	EVLP043101			
	1 1/4						EVLPJ044101		
150W	3/4	EVLP042151	EVLPBX042151	EVLPBX042151	EVLP042151	EVLP042151			EVLP04150
	1	EVLP043151	EVLPBX043151	EVLPBX043151	EVLP043151	EVLP043151			
	1 1/4						EVLPJ044151		
<b>Pulse Start Metal Halide</b>									
150W	3/4	EVLP092151S828	EVLPBX092151S828	EVLPBX092151S828	EVLP092151S828	EVLP092151S828			EVLP09150S828
	1	EVLP093151S828	EVLPBX093151S828	EVLPBX093151S828	EVLP093151S828	EVLP093151S828			
	1 1/4						EVLPJ094151S828		
175W	3/4	EVLP092171S828	EVLPBX092171S828	EVLPBX092171S828	EVLP092171S828	EVLP092171S828			EVLP09170S828
	1	EVLP093171S828	EVLPBX093171S828	EVLPBX093171S828	EVLP093171S828	EVLP093171S828			
	1 1/4						EVLPJ094171S828		
200W	3/4	EVLP092201S828	EVLPBX092201S828	EVLPBX092201S828	EVLP092201S828	EVLP092201S828			EVLP09201S828
	1	EVLP093201S828	EVLPBX093201S828	EVLPBX093201S828	EVLP093201S828	EVLP093201S828			
	1 1/4						EVLPJ094201S828		
250W	3/4	EVLP092251S828	EVLPBX092251S828	EVLPBX092251S828	EVLP092251S828	EVLP092251S828			EVLP09250S828
	1	EVLP093251S828	EVLPBX093251S828	EVLPBX093251S828	EVLP093251S828	EVLP093251S828			
	1 1/4						EVLPJ094251S828		
<b>Metal Halide</b>									
70W	3/4	EVLP092071	EVLPBX092071	EVLPBX092071	EVLP092071	EVLP092071			EVLP09070
	1	EVLP093071	EVLPBX093071	EVLPBX093071	EVLP093071	EVLP093071			
	1 1/4						EVLPJ094071		
100W	3/4	EVLP092101	EVLPBX092101	EVLPBX092101	EVLP092101	EVLP092101			EVLP09100
	1	EVLP093101	EVLPBX093101	EVLPBX093101	EVLP093101	EVLP093101			
	1 1/4						EVLPJ094101		
175W	3/4	EVLP092171	EVLPBX092171	EVLPBX092171	EVLP092171	EVLP092171			EVLP09170
	1	EVLP093171	EVLPBX093171	EVLPBX093171	EVLP093171	EVLP093171			
	1 1/4						EVLPJ094171		
250W	3/4	EVLP092251	EVLPBX092251	EVLPBX092251	EVLP092251	EVLP092251			EVLP09250
	1	EVLP093251	EVLPBX093251	EVLPBX093251	EVLP093251	EVLP093251			
	1 1/4						EVLPJ094251		

### Complete Catalog Number as follows:

Standard Voltage Ballasts – 60Hz									
1.									
Voltage Suffix	NEC/UL				CEC/CSA (cUL)				
	Multi Tap /MT	120V /120	480V /480	Tri Tap /TT	120V /120				
Optional Voltage Ballasts – 50 or 60Hz									
*CEC/CSA (cUL)– CWI Isolated Ballasts									
Voltage Suffix	*CEC/CSA (cUL)– CWI Isolated Ballasts				EXPORT				
	208V CWI /208CWI	240V CWI /240CWI	600V CWI /600CWI	220V 60Hz /220	220V 50Hz /220 50	230V 50Hz /230 50	240V 50Hz /240 50		

2. 150W HPS Luminaires only
- 55V lamps – add suffix "LX"
  - 100V lamps – add suffix "CE"
- Example: EVLP043151/MT-LX

†Ceiling and wall bracket mounts have 4 hubs; 3 are plugged.

\*CWI Isolated Ballasts are only available for high pressure sodium and 175W–250W metal halide (non pulse start) luminaires.

**4L**

# 4L EVLP Low Profile Hazard•Gard®

## Ordering by Components


**EVLP Luminaires are available in components.**

A complete luminaire consists of:

- Mounting Module
- Luminaire Body
- Guard, Dome Reflector or Angle Reflector

### Mounting Modules:

Type	Conduit	Cat. #
Pendant	3/4"	EVMP2
	1"	EVMP3
Ceiling & Wall Box	3/4"	EV22
	1"	EV33
Wall Bracket Arm	Use EV22 or EV33 box with EV87	EV87
Stanchion	1 1/4"	EVMJ4
<b>Guards</b>		
Medium		EV511
Mogul		EV512
<b>Reflectors</b>		
Dome		RD739
Angle		RA739



4L

**Medium Base Lamp Luminaires:**

Maximum Ambient	Watts	Class I, Group B (w/GB suffix) Groups C, D			Class II, Groups E, F, G Class III Simultaneous Presence		Supply Wire °C
		40°C	55°C	65°C	40°C		
High Pressure Sodium	70W	T5	T4A	T4A	T4A		90°C
	100W	T4A	T4A	T4	T4		90°C
	150W	T4	T3C	—	—		90°C
Metal Halide (including pulse start)	70W	T5	T4A	T4A	T4		85°C
	100W	T3C	T3C	—	—		90°C
	150W	T3C	T3B	—	—		90°C
	175W	T3C	T3B	—	—		90°C

**Mogul Base Lamp Luminaires:**

Maximum Ambient	Watts	Class I, Group B (w/GB suffix) Groups C, D			Class II, Groups E, F, G Class III Simultaneous Presence		Supply Wire °C
		40°C	55°C	65°C	40°C		
High Pressure Sodium	70W	T6	T5	T5	T5		90°C
	100W	T5	T4A	—	T4A		90°C
	150W	T4A	T4	—	T4		90°C
Metal Halide (including pulse start)	70W	T6	T5	T5	T5		85°C
	100W	T5	T4A	T4A	T4A		90°C
	150W	T4	T3C	—	T3C		90°C
	175W	T4	T3C	—	T3C		90°C
	200W	T3C	—	—	—		90°C
	250W	T3C	—	—	—		90°C

4L




# 4L EVLP Low Profile Hazard•Gard®

## Dimensions and Weights

### Dimensions In Inches:

	A	B	C	D	E	F
Medium Base	13.92	12.73	16.50	16.71	20.59	19.36
Mogul Base	15.69	14.69	18.25	18.46	22.34	21.30



### 4L Weights (lbs.):


Source	Watts	Luminaire w/guard	
		Medium	Mogul
High Pressure Sodium	70	34	36.5
	100	36	38.5
	150	36.5	39
Metal Halide	70	33.5	36
	100	34.5	37
	150	36	38.5
	175	36	38.5
	200	—	40.5
	250	—	40.5
<b>Add Mounting Modules:</b>		<b>Medium</b>	<b>Mogul</b>
Pendant		1	1
Ceiling		2	2
Bracket		4.5	4.5
Stanchion		2.5	2.5
<b>Add For Reflectors:</b>			
RA739		1	1
RD739		1	1
<b>Deduct for Wire Guard</b>		0.5	0.5

**Medium Base**

**Medium Base**

**Luminaire with Globe and Guard**


**EVLP143151 Lamp: 150W/B17 High Pressure Sodium (HPS)**



**Medium Base**

**Luminaire with Globe and Dome Reflector (Less Guard)**

**EVLP143150RD Lamp: 150W/B17 High Pressure Sodium (HPS)**



4L

# EVLP Low Profile Hazard•Gard®


Photometric Data

Medium and Mogul Base

## Medium Base

### Luminaire with Globe and 30° Angle Reflector (Less Guard)


EVLP143150RA Lamp: 150W/B17 High Pressure Sodium (HPS)



## Mogul Base

### Luminaire with Globe and Guard

EVLP14043151 Lamp: 150W/E23-1/2 High Pressure Sodium (HPS)




**Mogul Base**

**Mogul Base**

**Luminaire with Globe and Dome Reflector (Less Guard)**


**EVLP043150RD Lamp: 150W/E23-1/2 High Pressure Sodium (HPS)**



**Mogul Base**

**Luminaire with Globe and 30° Angle Reflector (Less Guard)**

**EVLP043150RA Lamp: 150W/E23-1/2 High Pressure Sodium (HPS)**



4L

# EVLP Low Profile Hazard®Gard®


## Mogul Base

Photometric Data

### Mogul Base

Luminaire with Globe and Guard

EVLP093171 Lamp: 175W/ED28 Metal Halide (MH)



CANDELAS		ZONAL LUMENS	
Mid-Zone Angle	Candelas	Zone	Lumens
0	2439	0-10	158
5	1750	10-20	313
15	1089	20-30	464
25	1017	30-40	563
35	915	40-50	732
45	917	50-60	922
55	1035	60-70	1128
65	1229	70-80	1377
75	1337	80-90	1473
85	1359	90-100	1452
95	1335	100-110	1257
105	1196	110-120	427
115	390	120-130	23
125	24	130-140	9
135	12	140-150	3
145	9	150-160	0
155	0	160-170	0
165	0	170-180	0
175	0		
180	0		

**\*Note:** Photometric data was developed using a 175 watt clear metal halide lamp (14,000 lumens). For other clear lamp wattages, use the following conversion factors (multipliers) with both candlepower distribution and isofootcandle charts. Multipliers do not apply to coefficients of utilization.

LAMP WATTS	CONVERSION FACTOR
70 W (MH)	0.40
100 W (MH)	0.56
250 W (MH)	1.46

LUMINAIRE SPACING RATIO – 0.4 (Spacing to mounting height ratio)  
(For additional photometric data, contact Crouse-Hinds)

**COEFFICIENTS OF UTILIZATION**  
Effective Floor Cavity Reflectance 20%

**ROOM CAVITY RATIO**

Eff. Ceil. Wall	0	1	2	3	4	5	6	7	8	9	10	
80°	70	82	70	62	56	51	46	43	39	36	34	31
70°	30	61	44	35	28	24	21	18	16	14	13	11
50°	10	82	56	42	33	28	23	19	17	14	13	11
30°	70	78	66	58	52	47	43	40	36	34	31	29
10°	50	78	61	51	44	38	34	30	27	24	22	20
0°	30	78	57	45	37	31	27	23	20	18	16	14
0°	10	78	53	40	32	26	22	18	16	14	12	11
0°	50	69	54	45	38	33	29	26	23	21	19	18
0°	10	69	50	40	33	28	24	21	18	16	14	13
0°	10	69	47	36	28	23	19	16	14	12	11	10
0°	50	61	47	39	33	29	26	23	20	19	17	16
0°	10	61	44	35	28	24	21	18	16	14	13	11
0°	10	61	42	31	25	21	17	15	12	11	10	9
0°	50	54	41	33	28	25	22	20	18	16	15	14
0°	10	54	37	27	22	18	15	13	11	10	8	7
0°	0	51	33	24	19	15	13	11	9	8	7	6

**ISOFOOTCANDLE CHART:**  
Footcandle Values for Isofootcandle Lines

Mtg. Hgt.	A	B	C	D	E	F
10'	20.00	10.00	5.00	2.00	1.00	0.50
12'	13.88	6.94	3.47	1.39	0.69	0.35
16'	7.82	3.91	1.96	0.78	0.39	0.20
20'	5.00	2.50	1.25	0.50	0.25	0.13
25'	3.20	1.60	0.80	0.32	0.16	0.08


**\*Percent Reflectance**

Isofootcandle chart shows illuminance in footcandles at ground level.

### Mogul Base

Luminaire with Globe and Dome Reflector (Less Guard)

EVLP093170RD Lamp: 175W/ED28 Metal Halide (MH)



CANDELAS		ZONAL LUMENS	
Mid-Zone Angle	Candelas	Zone	Lumens
0	3941	0-10	300
5	3241	10-20	763
15	2651	20-30	1249
25	2777	30-40	1399
35	2219	40-50	1594
45	2047	50-60	1671
55	1880	60-70	1466
65	1693	70-80	466
75	432	80-90	121
85	102	90-100	20
95	14	100-110	88
105	99	110-120	16
115	13	120-130	2
125	3	130-140	0
135	0	140-150	0
145	0	150-160	0
155	0	160-170	0
165	0	170-180	0
175	0		
180	0		

**\*Note:** Photometric data was developed using a 175 watt clear metal halide lamp (14,000 lumens). For other clear lamp wattages, use the following conversion factors (multipliers) with both candlepower distribution and isofootcandle charts. Multipliers do not apply to coefficients of utilization.

LAMP WATTS	CONVERSION FACTOR
70 W (MH)	0.40
100 W (MH)	0.56
250 W (MH)	1.46

LUMINAIRE SPACING RATIO – 1.0 (Spacing to mounting height ratio)

**COEFFICIENTS OF UTILIZATION**  
Effective Floor Cavity Reflectance 20%

**ROOM CAVITY RATIO**

Eff. Ceil. Wall	0	1	2	3	4	5	6	7	8	9	10	
70°	78	71	65	60	55	50	46	42	39	36	34	
80°	50°	78	69	60	53	47	42	37	33	30	27	25
30°	78	66	56	48	42	36	31	27	24	22	20	
10°	78	64	53	44	37	32	27	23	21	18	16	
0°	70°	76	70	64	58	53	49	45	41	38	35	33
0°	50°	76	67	59	52	46	41	37	33	30	27	24
0°	30°	76	65	55	47	41	36	31	27	24	22	19
0°	10°	76	62	52	44	37	32	27	23	20	18	16
0°	50°	72	64	57	50	45	40	35	31	29	26	24
0°	30°	72	62	53	46	40	35	30	27	24	21	19
0°	10°	72	60	51	43	37	31	27	23	20	18	16
0°	50°	69	61	54	48	43	38	34	30	28	25	23
0°	30°	69	60	52	45	39	34	30	26	23	21	19
0°	10°	69	58	49	42	36	31	26	23	20	18	16
0°	50°	66	58	52	46	41	37	33	30	27	24	22
0°	30°	66	58	50	43	38	33	29	26	23	20	18
0°	10°	66	56	48	41	35	30	26	23	20	18	16
0°	0°	65	55	47	40	34	29	25	21	19	16	14

**ISOFOOTCANDLE CHART:**  
Footcandle Values for Isofootcandle Lines

Mtg. Hgt.	A	B	C	D	E	F
10'	20.00	10.00	5.00	2.00	1.00	0.50
12'	13.88	6.94	3.47	1.39	0.69	0.35
16'	7.82	3.91	1.96	0.78	0.39	0.20
20'	5.00	2.50	1.25	0.50	0.25	0.13
25'	3.20	1.60	0.80	0.32	0.16	0.08

**\*Percent Reflectance**

Isofootcandle chart shows illuminance in footcandles at ground level.

**Mogul Base**

**Mogul Base**

**Luminaire with Globe and 30° Angle Reflector (Less Guard)**

**EVLPA093170RA Lamp: 175W/ED28 Metal Halide (MH)**

