



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EYD8 3" Female Drain Seal

Crouse-Hinds

Catalog Number	EYD8
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Eyd Conduit Sealing Fitting With Drain, Female, Feraloy Iron Alloy and/or Ductile Iron, Vertical Only, 3"
Weight per unit	10.3 (lbs/each)
Product Category	Sealing Bodies

Features

connection	Female Threaded, Female Threaded
dimensions	4.2500 IN X 4.2500 IN X 8.5000 IN

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Descriptions

Description	3" FEMALE DRAIN SEAL
extra long description	CRS-H EYD8 3 NPT THRU FEMALE CST IR
Features	In addition to restricting the passage of gases, vapors or flames from one portion of the electrical installation to another, Crouse-Hinds series EYD and EZD drain sealing fittings prevent accumulation of condensate above the seal. They are installed in vertical conduit runs and at low points in conduit systems.
Long Description	Eaton Crouse-Hinds series EYD conduit sealing fitting with drain, Female, Feraloy iron alloy and/or ductile iron, Vertical only, 3"
Product Type	3 NPT Thru Female CST Iron Drain Seal
Special Features	With Drain, Vertical Position

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274375809
Manufacturers Part Number	EYD8
UPC	782274375809

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Conduit sealing fitting with drain

Packaging

Carton	1
Weight Per each	10.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application.....	Ind Facilities & Factories - Industrial Facilities/Factories - Other.....
Enclosure.....	Class I Div 1 2 Group C D, Class II Div 1 2 Group F G, Class III.....
standard.....	UL 886, CSA C22.2.....