



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FD3200 FD 3P 600VAC Rated Load Terms Only

Eaton Corp

Catalog Number	FD3200
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, FD, Fixed Thermal and Magnetic Trips, Three-Pole, 200A, 600 Vac, 250 VDC, 65 Kaic At 240 Vac, 35 Kaic At 480 Vac, 1A-1B Rear W/Right Pigtail, 24 VDC Rear W/ Left Pigtail
Weight per unit	4.4 (lbs/each)
Product Category	3 Pole

Features

Current Rating	200 A
dimensions	3.3800 IN X 4.1300 IN X 6.0000 IN
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	FD 3P 600VAC RATED LOAD TERMS ONLY
extra long description	ETN FD3200LA06N02 FD 3P 200A L<ER
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, FD, Fixed thermal and magnetic trips, Three-pole, 200A, 600 Vac, 250 Vdc, 65 kAIC at 240 Vac, 35 kAIC at 480 Vac, 1A-1B rear w/right pigtail, 24 Vdc rear w/ left pigtail
Product Type	FD 3P 200A L&Lterm W/A1X1PK A/S&LST1LPK

Manufacturer Information

Brand	Eaton
GTIN	00782113491141
Manufacturers Part Number	FD3200LA06N02
UPC	782113491141

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 4.35

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

Frequency Rating 50 to 60 Hz

standard UL Listed