



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



G3X2LG6 SLTD Wiring Duct *Panduit Corporation*

Catalog Number	G3X2LG6
Manufacturer	Panduit Corporation
Description	The G3X2LG6 Panduct Lead-Free PVC Wide Slot Wiring Duct Feature A Wide Slot/Finger Design That Provides Greater Sidewall Rigidity and Is Suitable With A Range Of Wire Bundle Sizes. UL 94 Flame Class Of V-0 With A UL Recognized Continuous-Use Temperature Up to 122°F (50°C). Mounting Holes Provided. 3.0" X 2.0" (76.2. MM X 50.8 MM) and 6' (1.8 M) Long. Cover Sold Separately. Color Light Gray.
Weight per unit	0.0166 (lbs/each)
Product Category	Ducts, Raceways, Runways, Tray

Features

connection	Mounting Holes
Material	PVC
media	Yes

Material, Color, and Finish

Color	Light Gray
-------	------------

Dimensions and Weight

Length	6.00
Size	3.25 x 2.12
Width	3.25

Descriptions

Description	SLTD WIRING DUCT
extra long description	PAN G3X2LG6 Panduct® G3X2LG6 Base W
Long Description	The G3X2LG6 Panduct Lead-Free PVC Wide Slot Wiring Duct feature a wide slot/finger design that provides greater sidewall rigidity and is suitable with a range of wire bundle sizes. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). Mounting holes provided. 3.0" x 2.0" (76.2. mm x 50.8 mm) and 6' (1.8 m) long. Cover sold separately. Color Light Gray.
Product Type	Panduct® G3X2LG6 Base Wiring Duct

Manufacturer Information

Brand	PANDUIT
GTIN	00074983545872
Manufacturers Part Number	G3X2LG6
UPC	074983545872



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	WIRE DUCT AND COVERS
Type	Base Wiring Duct

Packaging

Carton	6
Package	120
Weight Per each	0.0166

Uses, Certifications, and Standards

Application	Wide slot/finger design provides greater sidewall rigidity and can be used in a wide range of applications
standard	RoHS Compliant, UL Recognized, CE Compliant; CSA Approved