

ELLIOTT ELECTRIC SUPPLY 1461 Technology Pkwy 30165-0000, GA Rome Phone: 706-622-4953 Fax: 706-622-4954



FNQR810 8/10A 600V TD Class CC Fuse

Bussmann Fuses

Catalog Number	FNQR810
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNQ-R Fuse, 0.8 A, Class CC,
	Non-Indicating, Ferrule End X Ferrule End, 12 Sec At 200%, 200
	Kaic, Melamine Tube, Standard, 600 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

0.8 A
Class CC
Ferrule End X Ferrule End
2.0000 IN X 0.5600 IN X 0.5600 IN
200 kAIC
Melamine Tube
Yes
600 V

Descriptions

Description	8/10A 600V TD CLASS CC FUSE
extra long description	EFSE FNQ-R-8/10 CLASS CC TIME DELAY
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Long Description	Eaton Bussmann series FNQ-R fuse, 0.8 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V
Product Type	Class CC Time Delay
Special Features	Rejection Style

Manufacturer Information

Brand	Eaton
GTIN	00051712147026
Manufacturers Part Number	FNQ-R-8/10
UPC	051712147026



standard

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy 30165-0000, GA Rome Phone: 706-622-4953 Fax: 706-622-4954

Taxonomies, Classifications, and Cate	gories
Category Description	MIDGET FUSES
Туре	FUSE
Packaging	
Carton	10
Weight Per each	0.02
Uses, Certifications, and Standards	
Application	Ind Facilities & Factories - Facility: Safety and Security Systems

CE Marked, RoHS Compliant