

Twist-Lock® Devices

30A, 125V AC, 2 Pole, 3 Wire Grounding

Single Flush Receptacle



Features

- Wire restraint recess for both back and side wiring, greatly reduces the possibility of loosening the terminal connection
- Face color coding by voltage facilitates locating and mating of proper devices
- All-brass mounting and grounding system provides a lower resistance ground path and greater resistance to corrosion than steel mounting systems

Ordering Information

| Description | Device Color | UPC | Catalog Number |
|----------------------|--------------|--------------|----------------|
| Nylon face, back and | Black | 783585235929 | HBL2610 |

Listings


Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

| | |
|-----------------|--|
| Face | Nylon |
| Base | Glass-Reinforced thermoplastic polyester (RTP) |
| Contacts | Brass |
| Terminal Screws | #10 - 32 Brass |
| Mounting Strap | Brass |

Performance

| | |
|-------------------------|--|
| Electrical | |
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |
| Mechanical | |
| Terminal Accommodation | #16 AWG - #8 AWG solid or stranded copper wire only. |
| Terminal Identification | Terminals identified in accordance with UL 498 |
| Environmental | |
| Flammability | V2 or better per UL94/CSA 22.2 No.0.17 |
| Moisture Resistance | IP20 Suitability |
| Operating Temperatures | Maximum Continuous 75°C; Minimum -40°C (w/o impact) |



Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

Accessories

| | |
|---------------------------------|---------------|
| Plug | HBL2611 |
| Wallplate or Weatherproof Cover | 1.60" Opening |
| Switched Enclosure | SETL3 |



Twist-Lock® Devices

30A, 125V AC, 2 Pole, 3 Wire Grounding

Single Flush Receptacle

Features

- Wire restraint recess for both back and side wiring, greatly reduces the possibility of loosening the terminal connection
- Face color coding by voltage facilitates locating and mating of proper devices
- All-brass mounting and grounding system provides a lower resistance ground path and greater resistance to corrosion than steel mounting systems

Ordering Information

| Description | Device Color | UPC | Catalog Number |
|----------------------|--------------|--------------|----------------|
| Nylon face, back and | Black | 783585235929 | HBL2610 |

Listings


Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

| | |
|-----------------|--|
| Face | Nylon |
| Base | Glass-Reinforced thermoplastic polyester (RTP) |
| Contacts | Brass |
| Terminal Screws | #10 - 32 Brass |
| Mounting Strap | Brass |

Performance

| | |
|-------------------------|--|
| Electrical | |
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |
| Mechanical | |
| Terminal Accommodation | #16 AWG - #8 AWG solid or stranded copper wire only. |
| Terminal Identification | Terminals identified in accordance with UL 498 |
| Environmental | |
| Flammability | V2 or better per UL94/CSA 22.2 No.0.17 |
| Moisture Resistance | IP20 Suitability |
| Operating Temperatures | Maximum Continuous 75°C; Minimum -40°C (w/o impact) |



Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

Accessories

| | |
|---------------------------------|---------------|
| Plug | HBL2611 |
| Wallplate or Weatherproof Cover | 1.60" Opening |
| Switched Enclosure | SETL3 |

