ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
9651 Camp Bowie West
76116-0000, TX Fort Worth
Phone: 817-560-0585
Fax: 817-560-0723



GHB3030 Type GHB BRKR 3P 30A 277/480VAC Max 125/250VDC Max

Eaton Corp

Catalog Number	GHB3030
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 30 A, 480Y/277 Vac, 125/250 VDC, 50/60 HZ
Weight per unit	1.8 (lbs/each)
Product Category	3 Pole

Features

Current Rating	30 A
dimensions	2.6300 IN X 3.0000 IN X 4.0000 IN
frame	G
interrupt rating	65 kAIC at 240 Vac14 kAIC at 480Y/277 Vac
media	Yes
Poles	Three-pole
Trip Type	T186
Voltage Rating	480Y/277 Vac, 125/250 Vdc

Descriptions

Description	TYPE GHB BRKR 3P 30A 277/480VAC MAX 125/250VDC MAX
extra long description	ETN GHB3030 GHB CB 3P 30A 277/480VA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 30 A, 480Y/277 Vac, 125/250 Vdc, 50/60 Hz
Product Type	GHB CB 3P 30A 277/480VAC Max 125/250VDC

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786679911273
Manufacturers Part Number	GHB3030
UPC	786679911273

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
9651 Camp Bowie West
76116-0000, TX Fort Worth
Phone: 817-560-0585
Fax: 817-560-0723

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Molded case circuit breaker

Availability

Status	Inactive

Packaging

Carton	1
Weight Per each	1.75

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies and EOEMs - Other
Frequency Rating	50/60 Hz
standard	UL Listed,Federal Specifications Classification W-C375B