



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL2741 LKG Plug, 30A 3P 600V, L17-30P, B/W** *Hubbell Wiring Devices*

Catalog Number	HBL2741
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 3-Phase 600V Ac, 3-Pole 4-Wire Grounding, L17-30P, Screw Terminal, Black and White
Weight per unit	0.3000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### **Features**

amperage rating	30
connection	Screwed Terminal
Cord Type	All Listed Portables
Current Rating	30
Material	Nylon
Number of Wires	4-Wire
pallet quantity	2880
Phase	3
Poles	3-Pole
Voltage Rating	3 Phase 600 VAC
Wattage	18
Wire Size	#16 to #8

### **Material, Color, and Finish**

Color	BLACK, WHITE
-------	--------------

### **Dimensions and Weight**

Size	2.33 in x 2.33 in x 2.75 in
------	-----------------------------

### **Descriptions**

Description	LKG PLUG, 30A 3P 600V, L17-30P, B/W
extra long description	HWDK HBL2741 LKG PLUG, 30A 3P 600V,
Long Description	Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 3-Phase 600V AC, 3-Pole 4-Wire Grounding, L17-30P, Screw Terminal, Black and White
Product Type	LKG Plug, 30A 3P 600V, L17-30P, B/W
Special Features	Standard Product

### **Manufacturer Information**

Brand	Hubbell Wiring Devices
GTIN	00783585039374
Manufacturers Part Number	HBL2741
UPC	783585039374



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Plugs

## Packaging

Carton	1
Package	30
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Extra Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	L17-30P
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498