

GRC58, Mechanical Ground Rod Clamp, Cable to Rod

By Burndy
Catalog # [GRC58](#)



Mechanical Ground Rod Clamp, For Cable to Rod, High Strength, 10 AWG (Sol)- 1 AWG (Str), 5/8" Drive Rod, 3/8" Stud.

Application

For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Direct Burial Applications In Earth And Concrete

General

EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	170 in-lb
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GRC, High Strength
UPC	781810230961
UPC 12 Digit	7818102309611

Dimensions

Dimension - B Length inch	0.57 in
Dimension - Height inch	2.18 in
Dimension - Length Side B inch	0.63 in
Dimension - Width inch	0.95 in
Dimension - Width mm	24 mm

Conductor Related

Conductor - Copper Solid Size Range	10 AWG
Conductor - Copper Str Size Range	12 AWG-1 AWG
Conductor - Rod Size	5/8 in
Conductor Size	#10 AWG Sol - #1 AWG Str
Conductor Type	<ul style="list-style-type: none"> Rod-Size CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	27500

Product Assets

[3D Models - GRC58_MODEL-IGES](#)
[3D Models - GRC58_MODEL-PDF](#)
[3D Models - GRC58_MODEL-STEP](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SA..076868-01](#)