



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL7810D 30A 600V 3P Disc SW *Hubbell Wiring Devices*

Catalog Number	HBL7810D
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Industrial Grade, Manual Motor Controllers, Motor Disconnects, Three Pole, 30A 600V Ac, Back and Side Wired, Black
Weight per unit	0.5500 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

### Features

connection	Pressure Screw Terminals
Current Rating	30
Enclosure Type	None
Material	Stainless Steel
Number of Phases	Three
Poles	3 Pole
Power Rating	18000
terminals	Terminal Screws
Voltage Rating	600

### Dimensions and Weight

Size	Standard Sized Product
------	------------------------

### Descriptions

Description	30A 600V 3P DISC SW
extra long description	HWDK HBL7810D 30A 600V 3P DISC SW
Long Description	Switches and Lighting Controls, Industrial Grade, Manual Motor Controllers, Motor Disconnects, Three Pole, 30A 600V AC, Back and Side Wired, Black
Product Type	30A 600V 3P Disc SW
Special Features	Standard Product

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585202792
Manufacturers Part Number	HBL7810D
series	Standard Toggle
UPC	783585202792

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Back & Side Wire



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1

Weight Per each ..... 0.55

## Uses, Certifications, and Standards

Application ..... Motor Starting w/o Overload Protection

Mounting ..... Screw Mount

standard ..... CSA-C22.2 No.14 Industrial Control File LR-46186;UL 508,  
Industrial Control File #E70402

Temperature Rating ..... Minimum Continuous -40 Deg C without Impact