



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBLDS60100RS Rep Disco Switch, 60A, *Hubbell Wiring Devices*

Catalog Number	HBLDS60100RS
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Replacement Switch, Three Pole, 60A 600V Ac, Screw Terminals, Gray
Weight per unit	1.4 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

### Features

amperage rating	60/100
connection	Terminal Screws
Contact Configuration	Two Position
Contact Rating	100A
Material	COMPOSITE
Poles	3

### Dimensions and Weight

Size	Standard Sized
------	----------------

### Descriptions

Description	REP DISCO SWITCH, 60A,
extra long description	HWDK HBLDS60100RS REP DISCO SWITCH,
Features	NEC section 430.102(B) requires each motor controller to have a disconnect within line of sight from the motor and driven equipment. Hubbell's Circuit-Lock® Unfused Disconnect Switches are UL listed as a manual motor controller and also "suitable as a motor disconnect" and meet these code requirements.
Long Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Replacement Switch, Three Pole, 60A 600V AC, Screw Terminals, Gray
Product Type	Rep Disco Switch, 60A,
Special Features	Standard Product

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	0078358595216
Manufacturers Part Number	HBLDS60100RS
series	Fused;Non-Fused
UPC	78358595216



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Accessories

## Packaging

Carton	1
Package	10
Weight Per each	1.35

## Uses, Certifications, and Standards

Application	For 60 and 100A HBLDS6 Series
environmental conditions	Indoor Dry unless protected by additional means
standard	UL Listed