




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HDVBC2G 2/0 CBL to 24" STL Surface HD "VB" Mold

Erico, Inc. Eritec-Caddy

| | |
|------------------|--|
| Catalog Number | HDVBC2G |
| Manufacturer | Erico, Inc. Eritec-Caddy |
| Description | Cable to Steel, Heavy Duty, VB, Steel Pipe or Flat Surface, 2/0 Concentric |
| Weight per unit | N/A |
| Product Category | Ground Rods & Grounding System |

Features

| | |
|----------------|----------------|
| Conductor Size | 2/0 Concentric |
| media | Yes |
| Pipe Size | 24 |

Dimensions and Weight

| | |
|----------------|-------|
| Outer Diameter | 609.6 |
|----------------|-------|

Descriptions

| | |
|------------------------|---|
| Description | 2/0 CBL TO 24" STL SURFACE HD "VB" MOLD |
| extra long description | NVENT EFS HDVBC2G MOLD,CABLE TO VER |
| Features | Heavy duty connections were originally developed to be used on reclaimed cable. The heavy duty connections use a larger size connection cavity in the mold and a larger size welding material than the equivalent standard duty connection. |
| Long Description | Cable to Steel, Heavy Duty, VB, Steel Pipe or Flat Surface, 2/0 Concentric |
| Product Type | Mold, Cable to Vert STL, Vert Tap Down |
| Short Description | MOLD,CABLE TO VERT STL,VERT TA |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | nVent ERICO |
| GTIN | 00782856542490 |
| Manufacturers Part Number | HDVBC2G |
| UPC | 782856542490 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | EXOTHERMIC GROUNDING PRODUCTS |
| Type | Heavy Duty Molds |

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Weight Per each | 0 |

Uses, Certifications, and Standards

| | |
|-------------|-----------------------|
| Application | Grounding and Bonding |
|-------------|-----------------------|