

Straight Blade Devices
20A, 125V, 2 Pole, 3 Wire Grounding
Insulgrip Connector

HUBBELL

Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Fast lead assembly screws
- Beveled housing prevents snagging

Ordering Information

| Description | Cord Diameter | UPC | Catalog Number |
|-----------------------|-----------------------|--------------|----------------|
| Black and white nylon | .230"-.720"(5.8-18.3) | 783585174259 | HBL5369C |

Listings

UL Listed to UL498 File E1706
CSA Certified to C22.2 No. 42 File 280
NEMA® WD-6 Compliant

Specifications

| | |
|--------------------|------------------------------|
| Housing/Cord Clamp | Nylon |
| Contact Holder | Nylon |
| Terminal Retainer | Clear Polycarbonate |
| Contacts | .040 in. (1.0) Brass |
| Terminal Screws | #8-32 Brass , multiple drive |
| Terminal Clamp | Nickel plated steel |
| Assembly Screws | Nickel plated steel |

Performance

Electrical


Current Interrupting Certified for current interrupting at full rated current
Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device
Terminal Accommodation #18-10 AWG copper conductors only
Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability UL 94 HB or better
IP Suitability IP20
Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)



Accessories

Weatherproof Boot HBL6018

Resources

Customer Use Drawing
eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



Straight Blade Devices
20A, 125V, 2 Pole, 3 Wire Grounding
Insulgrip Connector

HUBBELL

Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Fast lead assembly screws
- Beveled housing prevents snagging

Ordering Information

| Description | Cord Diameter | UPC | Catalog Number |
|-----------------------|-----------------------|--------------|----------------|
| Black and white nylon | .230"-.720"(5.8-18.3) | 783585174259 | HBL5369C |

Listings

UL Listed to UL498 File E1706
CSA Certified to C22.2 No. 42 File 280
NEMA® WD-6 Compliant

Specifications

| | |
|--------------------|------------------------------|
| Housing/Cord Clamp | Nylon |
| Contact Holder | Nylon |
| Terminal Retainer | Clear Polycarbonate |
| Contacts | .040 in. (1.0) Brass |
| Terminal Screws | #8-32 Brass , multiple drive |
| Terminal Clamp | Nickel plated steel |
| Assembly Screws | Nickel plated steel |

Performance

Electrical


Current Interrupting Certified for current interrupting at full rated current
Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device
Terminal Accommodation #18-10 AWG copper conductors only
Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability UL 94 HB or better
IP Suitability IP20
Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)



Accessories

Weatherproof Boot HBL6018

Resources

Customer Use Drawing
eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

