



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL9452C Plug, Ang, 3P4W, 50A 125/250V, 14-50P** *Hubbell Wiring Devices*

Catalog Number	HBL9452C
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Male Plug, Nylon, 4-Position, Heavy Duty, Industrial/Commercial Grade, Angled, 3-Pole 4-Wire Grounding, 50A 125/250V, 14-50P, Black, Single Pack.
Weight per unit	0.8000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### **Features**

amperage rating	50
connection	Screwed Terminal
Cord Type	All Portable
Current Rating	50
Material	Nylon
Number of Wires	4-Wire
pallet quantity	765
Phase	1
Poles	3-Pole
Voltage Rating	125;250
Wattage	12500;12500.0000
Wire Size	#12 to #4

### **Material, Color, and Finish**

Color	Black
-------	-------

### **Dimensions and Weight**

Size	4.5 in x 3.38 in x 2.37 in
------	----------------------------

### **Descriptions**

Description	PLUG, ANG, 3P4W, 50A 125/250V, 14-50P
extra long description	HWDK HBL9452C PLUG, ANG, 3P4W, 50A
Long Description	Straight Blade Devices, Male Plug, Nylon, 4-Position, Heavy Duty, Industrial/Commercial Grade, Angled, 3-Pole 4-Wire Grounding, 50A 125/250V, 14-50P, Black, Single Pack.
Product Type	Plug, Ang, 3P4W, 50A 125/250V, 14-50P
Special Features	Angled, 4-Position



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Hubbell Wiring Devices
GTIN	00783585015330
Manufacturers Part Number	HBL9452C
series	Extra Heavy Duty
UPC	783585015330

## Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	PLUG

## Packaging

Carton	1
Package	5
Weight Per each	0.8

## Uses, Certifications, and Standards

Application	Industrial/Commercial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	14-50P
standard	UL Listed To UL498 File E1706, CSA Certified To C22.2 No. 42 File 280