

NEER Zinc Pulling Ells and PVC Entrance Caps

Threaded for Rigid Conduit and IMC

HL: 90° Female/Female Pulling Ells

Applications

- Threaded 90° corner pulling elbows are used to facilitate pulling conductors through a sharp bend in a run of threaded rigid conduit or IMC.

Features

- Raintight (wet locations).
- The removable cover gives ample access so that wire pulling can be achieved without any obstructions.

Standard Material


- Zinc diecast

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E32539
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 208044
- NEMA: FB-1



HL-500



| Trade Size (Inches) | Catalog Number | Dimensions in Inches/Millimeters | |
|---------------------|----------------|----------------------------------|-----------|
| | | A | B |
| 1/2 | HL-500 | 2.10/53.3 | 2.10/53.3 |
| 3/4 | HL-750 | 2.29/58.2 | 2.29/58.2 |

PVC: Entrance Caps

Applications

- Plastic entrance caps for rigid conduit, IMC, EMT or PVC conduit service mast.

Features

- Cover releases with screwdriver twist, no screws to back out.
- U-slots eliminate cumbersome two piece insulator.
- Complete with EMT adapter.

Standard Material


- PVC

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E302405
- NEMA: FB-1



PVC-100



| Trade Size (Inches) | Catalog Number | Dimensions in Inches/Millimeters | |
|---------------------|----------------|----------------------------------|------------|
| | | A | B |
| 1/2 | PVC-100 | 2.90/73.7 | 2.63/66.8 |
| 3/4 | PVC-101 | 3.17/80.5 | 3.15/80.0 |
| 1 | PVC-102 | 3.35/85.1 | 3.11/79.0 |
| 1-1/4 | PVC-103 | 3.90/99.1 | 3.70/94.0 |
| 1-1/2 | PVC-104 | 3.80/96.5 | 3.77/95.8 |
| 2 | PVC-105 | 6.25/158.8 | 6.50/165.1 |