



Surge Protection: Whole House Surge Protection

Smart Guard[®] Whole House Surge Protective Device with IModule[™] | IG2240-IMSK

Smart Guard[®] Whole House Surge Protective Device with IModule[™]

IG2240-IMSK

Intermatic's Smart Guard[®] Whole House Surge Protective Device provides coverage of your customer's big investment equipment, from appliances and computers, to HVAC equipment and TVs. This innovative SPD uses the IModule[™] with LED lights for quick and easy indication when protection has been compromised. A blue light indicates the SPD unit is ON and a green light indicates surge protection is active. Trusted, state-of-the-art TPMOV[®] (Thermally Protected Metal Oxide Varistor) surge protection technology eliminates the potentially hazardous failure modes that are commonly associated with standard MOV technology. Type 1 applications include outdoor installations before service entrances and utility meter cabinets. Type 2 applications include installations after service entrances. UL Listed to ANSI/UL 1449 3rd edition



Features & Applications

Features

- Six Modes of protection
- TPMOV[®] surge protection technology
- Module Power Switch, included on IG2240-IMSK, enables convenient disconnection of power at the SPD when replacing IModules
- Includes three IModules with LED power and protection status lights
- IModules replace quickly and easily, eliminating the need to install a new SPD unit

Applications

- Residential
- Light Commercial

- Tamper-proof IModule doors, will only open when IModule is being inserted
- Includes the IG2200-FMK flush mount kit
- Type 1 Enclosure for indoor applications in metal
- 10-year product warranty
- \$50,000 connected equipment warranty for 10 years on appliances and electronics
- UL certified to ANSI/UL 1449 3rd edition

System Includes

System Includes (1)



IG2200-FMK

**FLUSH MOUNT KIT FOR IG2240-IMSK AND
IG2280-IM**

Qty: 1

Specifications

Surge Protection Type

1, 2

Nominal Discharge Current

10 kA

Short Circuit Current Rating

10 kA

Surge Protection
TPMOV®

Wiring Option

Terminals, Wire Leads

Enclosure Type

Indoor Type 1 Metal

Maximum Continuous Operating Voltage (L-G)

300

Maximum Continuous Operating Voltage (L-L)

300

Maximum Continuous Operating Voltage (L-N)

150

Maximum Continuous Operating Voltage (N-G)

150

Voltage Protection Rating (L-G)

1500

Voltage Protection Rating (L-L)

1500

Voltage Protection Rating (L-N)

800

Voltage Protection Rating (N-G)

700

Operating Temperature Max (°C)

85

Operating Temperature Max (F)

185

Operating Temperature Min (°C)

-35

Operating Temperature Min (F)

-31

Number of Wire Leads

4

Wire Lead Length (in)

32

Wire Lead Length (mm)

812.8

Warranty

10-year

Connect Equipment Warranty Period

10-year

Videos

Related Accessories and Parts (1)



IModule™ Replacement Module for
Smart Guard

IG120RSM10K



Copyright © 2017 Intermatic Incorporated. All rights reserved.



Surge Protection: Whole House Surge Protection

Smart Guard[®] Whole House Surge Protective Device with IModule[™] | IG2240-IMSK

Smart Guard[®] Whole House Surge Protective Device with IModule[™]

IG2240-IMSK

Intermatic's Smart Guard[®] Whole House Surge Protective Device provides coverage of your customer's big investment equipment, from appliances and computers, to HVAC equipment and TVs. This innovative SPD uses the IModule[™] with LED lights for quick and easy indication when protection has been compromised. A blue light indicates the SPD unit is ON and a green light indicates surge protection is active. Trusted, state-of-the-art TPMOV[®] (Thermally Protected Metal Oxide Varistor) surge protection technology eliminates the potentially hazardous failure modes that are commonly associated with standard MOV technology. Type 1 applications include outdoor installations before service entrances and utility meter cabinets. Type 2 applications include installations after service entrances. UL Listed to ANSI/UL 1449 3rd edition



Features & Applications

Features

- Six Modes of protection
- TPMOV[®] surge protection technology
- Module Power Switch, included on IG2240-IMSK, enables convenient disconnection of power at the SPD when replacing IModules
- Includes three IModules with LED power and protection status lights
- IModules replace quickly and easily, eliminating the need to install a new SPD unit


Applications

- Residential
- Light Commercial

- Tamper-proof IModule doors, will only open when IModule is being inserted
- Includes the IG2200-FMK flush mount kit
- Type 1 Enclosure for indoor applications in metal
- 10-year product warranty
- \$50,000 connected equipment warranty for 10 years on appliances and electronics
- UL certified to ANSI/UL 1449 3rd edition

System Includes

System Includes (1)



IG2200-FMK

**FLUSH MOUNT KIT FOR IG2240-IMSK AND
IG2280-IM**

Qty: 1

Specifications

Surge Protection Type

1, 2

Nominal Discharge Current

10 kA

Short Circuit Current Rating

10 kA

Surge Protection
TPMOV®

Wiring Option

Terminals, Wire Leads

Enclosure Type

Indoor Type 1 Metal

Maximum Continuous Operating Voltage (L-G)

300

Maximum Continuous Operating Voltage (L-L)

300

Maximum Continuous Operating Voltage (L-N)

150

Maximum Continuous Operating Voltage (N-G)

150

Voltage Protection Rating (L-G)

1500

Voltage Protection Rating (L-L)

1500

Voltage Protection Rating (L-N)

800

Voltage Protection Rating (N-G)

700

Operating Temperature Max (°C)

85

Operating Temperature Max (F)

185

Operating Temperature Min (°C)

-35

Operating Temperature Min (F)

-31

Number of Wire Leads

4

Wire Lead Length (in)

32

Wire Lead Length (mm)

812.8

Warranty

10-year

Connect Equipment Warranty Period

10-year

Videos

Related Accessories and Parts (1)



IModule™ Replacement Module for Smart Guard

IG120RSM10K



Copyright © 2017 Intermatic Incorporated. All rights reserved.