

**HU20**  
Undercabinet lighting

**HALO**



**EATON**

*Powering Business Worldwide*

## HU20 Magnetic Puck LED Undercabinet




**Halo introduces the next generation of HU20 to address your LED Undercabinet and task lighting needs.**

Ideal for task, accent, office, cove, utility and display lighting, the Halo Undercabinet low-profile design delivers maximum energy savings and long life. The magnetic puck system offers supreme flexibility in both the length of track, and the position of the luminaires. The new 90 CRI magnetic pucks feature a strong magnetic connection and offer 150 lumens per puck. The system utilizes a new sensitive touch driver. To operate, simply tap the HALO logo and the fixture will illuminate. Tap the logo multiple times to adjust the lighting levels (100%/70%/40%/0%). This new touch sensitive driver is smaller in size and connects directly to the track. A 6" connector cable makes it easy to link one unit of track to another. The track can be field cut to size and is offered in three different standard sizes of 12", 18" and 24".



## Installer friendly features



**LINKABLE**



**PLUG-IN**



**LIGHT LEVELS**

High / Med / Low / Off

Each system can be mounted horizontally with just a few fasteners and is packaged with all required mounting hardware. Quick connect features make linking fixtures together quick and easy. Each track can be field cut to the desired length.

- 87% energy savings compared to halogen
- Lasts up to 22 years
- 3000K, 90 CRI
- Sleek profile of 1" including driver on the track
- Sensitive touch driver
- Convenient direct plug-in
- Place up to 7 pucks on one driver
- Damp location listed for indoor use
- ENERGY STAR®
- 120V only
- Five-year warranty



HU20G212MB - 12"



HU20G218MB - 18"



HU20G224MB - 24"

HU20G2xxMB

Track



HU20G2P930MB

Puck



HU20G2D13MB

Sensitive touch driver



HU20G22MB

Connector




Tap the **HALO** logo on the driver to control the light source.

- TAP 1** HIGH (100% light output)
- TAP 2** MID (70% light output)
- TAP 3** LOW (40% light output)
- TAP 4** OFF (0% light output)

## Energy Data

12" Fixture		
Lumens:	340	
120V Input Watts:	4.7	
LPW:	72.3	

18" Fixture		
Lumens:	504	
120V Input Watts:	7.0	
LPW:	72.1	

24" Fixture		
Lumens:	660	
120V Input Watts:	9.24	
LPW:	71.4	


Energy data with 7 pucks: 1114 lumens, 14.7 Watts, 75.8 LPW

<b>Power Factor:</b>	>0.88 <sup>A</sup>
<b>Color Temperature:</b>	3000K
<b>Color Rendering Index:</b>	90

<sup>A</sup>Nominal data with 4 pucks.



Qualified and compliant. Refer to ENERGY STAR® Qualified Products List for listings.  
Can be used to comply with California Title 24 High Efficacy requirements.

<b>BRIGHTNESS</b> <b>300</b> lumens	<b>REPLACES</b> <b>20W</b> bulbs**	<b>UP TO</b> <b>\$120</b> savings*	
---	--	--	---

\*Over the life of the fixture Energy Savings: \$120.60 Savings based on \$0.11 per kilowatt hour and 6 hours average use per day and 50,000 hours of lamp life, lumen equivalent to fixture with (1) 20W halogen lamps  
\*\* 6 hours average use per day




## Ordering Information / Dimensions

### Track<sup>o</sup>

Sample Number: **HU20G212MB** (12" Track Matte Black)

System	Length	Finish
<b>HU20G2</b> = Halo LED Undercabinet	<b>12</b> = 12" <b>18</b> = 18" <b>24</b> = 24"	<b>MB</b> = Matte Black




<sup>o</sup>Horizontal mounting only.

### Puck

Sample Number: **HU20G2P930MB** (Puck 90CRI, 3000K, Matte Black)


System	Form Factor	CRI	Color Temperature	Finish
<b>HU20G2</b> = Halo LED Undercabinet	<b>P</b> =Puck	<b>9</b> =90 CRI	<b>30</b> =3000K	<b>MB</b> = Matte Black



### Driver

Sample Number: **HU20G2D13MB**  
(13W driver, Matte Black)


System	Form Factor	Wattage	Finish
<b>HU20G2</b> = Halo LED Undercabinet	<b>D</b> =Corded	<b>13</b> =13 Watts	<b>MB</b> = Matte Black



### Connector

Sample Number: **HU20G22MB** (6" connector, Matte Black)

System	Length	Finish
<b>HU20G2</b> = Halo LED Undercabinet	<b>2</b> =6" connector	<b>MB</b> = Matte Black



## **Eaton**

1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
[www.eaton.com/lighting](http://www.eaton.com/lighting)

## **Canada Sales**

5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

## **Our Lighting Product Lines**

Halo  
Halo Commercial  
Portfolio  
IRiS  
RSA  
Metalux  
Corelite  
Neo-Ray  
Fail-Safe  
MWS  
Ametrix  
Shaper  
io  
Lumark  
McGraw-Edison  
Invue  
Ephesus  
Lumière  
Streetworks  
AtLite  
Sure-Lites

## **Our Controls Product Lines**

Greengate  
iLumin  
Zero 88  
Fifth Light Technology  
iLight (International Only)

## **Eaton**

1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
[www.eaton.com/lighting](http://www.eaton.com/lighting)

© 2016 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. BR518027EN  
October 2016

Products, specifications and compliances are subject to change without notice.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



*Powering Business Worldwide*