



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HUB150DN 1-1/2" Rigid Watertite D/C Hub *Appleton/Oz Gedney*

Catalog Number	HUB150DN
Manufacturer	Appleton/Oz Gedney
Description	Watertight Hubs, Zinc Diecast Hubs - Insulated, Class I, Div 2, Trade Size: 1-1/2", Body Length: 1.12", Thread Length: 0.78", Outside Diameter: 2.75"
Weight per unit	0.7000 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

Material	Zinc Die Cast
----------	---------------

Dimensions and Weight

Size	1-1/2
------	-------

Descriptions

Description	1-1/2" RIGID WATERTITE D/C HUB
extra long description	EGS HUB150DN 1-1/2 ZDC WATER TIGHT
Long Description	Watertight Hubs, Zinc Diecast Hubs - Insulated, Class I, Div 2, Trade Size: 1-1/2", Body Length: 1.12", Thread Length: 0.78", Outside Diameter: 2.75"
Product Type	1-1/2 ZDC Water Tight Hubs
Special Features	1-1/2 IN Trade Size Hub, Hole Dia. Min 1.92 IN, Hole Dia. Max 2.02 IN, Panel Thickness Min. 0.06 IN, Panel Thickness Max. 0.25 IN, Insulated Throat

Manufacturer Information

Brand	Appleton
GTIN	00687855002153
Manufacturers Part Number	HUB150DN
UPC	687855002153

Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Watertight Hubs

Packaging

Carton	10
Package	50
Weight Per each	0.7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Used to Connect Rigid or IMC Conduit to a Threadless Opening in an Enclosure

standard

CSA Certified: 065178; CSA Standard: C22.2 No. 18.3; NEMA: FB-1; UL Listed: E14814; UL Standard: 514B