



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L11T836G8CSJDX2 11W Led T8 36" 3K/35K/4K/5K/65K SGL/DBL End-Glass

Keystone Technologies

Catalog Number	L11T836G8CSJDX2
Manufacturer	Keystone Technologies
Description	11W Led T8 Tube, 1500 Lumen, Glass Construction, 3FT, Color Select 3000/3500/4000/5000K/6500K, 120-277V Input, Direct Drive, Single and Double Ended Wiring
Weight per unit	0.0200 (lbs/each)
Product Category	Lighting

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
Lamp Type	T8
lumens	1500
Nominal Length	36 in
Nominal Size	N/A
Number of Lamps	Not Applicable - No Bulb
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	11
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
housing color	N/A

### Descriptions

Construction	Frosted Glass
Description	11W LED T8 36" 3K/35K/4K/5K/65K SGL/DBL END-GLASS
extra long description	Key KT-LED11T8-36G-8CSJ-DX2 11W LED
Long Description	11W LED T8 Tube, 1500 lumen, Glass Construction, 3ft, Color Select 3000/3500/4000/5000K/6500k, 120-277v Input, Direct Drive, Single and Double Ended Wiring
Product Type	11W Led T8 Tube, 1500 Lumen, Glass Construction, 3FT, Color



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654141435
Manufacturers Part Number	KT-LED11T8-36G-8CSJ-DX2
UPC	843654141435

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
Weight Per each	0.02

## Uses, Certifications, and Standards

Energy Star	N
-------------	---