


ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685





IPLD2504 250MCM-#6 4 Pole Polaris Connector Block Nsi Industries

Catalog Number	IPLD2504	
Manufacturer	Nsi Industries	
Description	Multi-Tap Connector, #6 Awg Conductor Size, 250 MCM Conductor Size, Insulated, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, 4 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 3.8 In Overall Length, 600 V, 0.47 LB/Ea	
Weight per unit	0.4700 (lbs/each)	
Product Category		
eatures		
Poles	1	
Voltage Rating	600 V	
Warranty		
Wire Size	250 MCM-6 AWG	
Wire Type	Class B & C	
Material, Color, and Finish		
Color	Black	
Finish	Plastisol Insulated	
Housing Material	Aluminum	
imensions and Weight		
Size	L=3.800 - W=2.280 - H=2.180	
escriptions		
Description	250MCM-#6 4 POLE POLARIS CONNECTOR BLOCK	
extra long description	NSI IPLD250-4 CIr 250-6AWG Insltd M	
Features	The Polaris IPLD250-4 4-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to four conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 250 MCM - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum-alloy body is wrapped in high-dielectric stre	
lanufacturer Information		
GTIN	00662381923028	
UPC	662381923028	



standard

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Taxonomies, Classifications, and	Categories	
Category Description	SPLIT BOLTS	
Туре	Double Sided Entry	
Packaging		
Carton	6	
Weight Per each	0.47	
Uses, Certifications, and Standar	ds	
Application	Wire Termination	
environmental conditions	90 C	

UL 486A/B