



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L515P Turnlok Plug 3W 15A 125V

Pass & Seymour/LeGrand

| | |
|------------------|--------------------------------|
| Catalog Number | L515P |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Turnlok® Plug 3-Wire 15A 125a |
| Weight per unit | 0.1600 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|-------|
| amperage rating | 15 |
| Material | Nylon |
| Number of Wires | 3 |
| Poles | 2 |
| Voltage Rating | 125 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|-------|-------------|
| Color | Black&White |
|-------|-------------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.8 in |
|------|--------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | TURNLOK PLUG 3W 15A 125V |
| extra long description | P&S PSL515P TURNLOK PLUG 3W 15A 125 |
| Long Description | Turnlok® Plug 3-Wire 15A 125A |
| Product Type | Turnlok Plug 3W 15A 125V |
| Special Features | Locking Device, impact resistant |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007236545 |
| Manufacturers Part Number | PSL515P |
| UPC | 785007236545 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Industrial cord connectors |
| Type | Turnlock Plug |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.16 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|-----------------------|
| Application | Industrial Spec Grade |
| Mounting | Plug |
| nema rating | L5-15P |
| standard | UL 498 |