



# KT-LED36PSHID-EX39-8CSB-D HID REPLACEMENT LED LAMP

#### **DESCRIPTION**

Power Select + Color Select 36W HID Replacement LED Lamp | 80 CRI | IP64









LAMP TYPE: HID Replacement LED


BASE TYPE: EX39 (Mogul)

**SELECTABLE WATTAGE:** 36/27/18W

SELECTABLE COLOR TEMPERATURE: 3000/4000/5000K

**METAL HALIDE EQUIVALENT: 150W COLOR RENDERING INDEX (CRI):** >80

**WARRANTY:** 5 Years



#### **PRODUCT FEATURES**

- Replacement for conventional metal halide lamp
- Keystone Power Select Technology (36/27/18W)
- Keystone Color Select Technology (3000/4000/5000K)
- 50.000 + hour lifetime
- Environmentally friendly: No mercury used
- Instant startup
- Operating temperature: -40°C/-40°F to 60°C/140°F
- UL listed

- Integral driver, eliminates the need for external driver or ballast; includes 4kV surge protection
- IP64 rated; integrated heat sink quickly dissipates heat and guides water intrusion out of the lamp
- Suitable for use in fully enclosed fixture. Minimum lamp compartment dimensions: 8in x 8in x 9in
- Do not use with standard dimmers. Not compatible with phase dimmers. Dimming functions with sensors only

#### **ELECTRICAL AND PERFORMANCE SPECIFICATIONS**

Keystone Catalog Number	Input Voltage	Selectable Power	Selectable CCT	Lumens	Efficacy	Base Type	CRI	Input Current
	120-277V	36W	3000K	4860 lm	135 lm/W	EX39	>80	0.30A @ 120V 0.13A @ 277V
KT-LED36PSHID-EX39-8CSB-D			4000K	5220 lm	145 lm/W			
			5000K	5040 lm	140 lm/W			
	120–277V	27W	3000K	3645 lm	135 lm/W			0.23A @ 120V 0.10A @ 277V
			4000K	3915 lm	145 lm/W			
			5000K	3780 lm	140 lm/W			
	120–277V	18W	3000K	2430 lm	135 lm/W			0.15A @ 120V 0.06A @ 277V
			4000K	2610 lm	145 lm/W			
			5000K	2520 lm	140 lm/W			

<sup>\*</sup> Color Uniformity: CCT (Correlated Color Temperature) range as per guidelines outlined in ANSI C78.377-2017







# KT-LED36PSHID-EX39-8CSB-D HID REPLACEMENT LED LAMP

### **SMART PORT LED**



On the top of the lamp is a low-voltage AUX port for lamp level sensor controls.

#### **SMART PORT LED AUX SENSORS**



<sup>\*</sup> For use with continuous dimming applications.

#### WIRING INSTRUCTIONS

#### STEP 1


Disconnect power. Disconnect and remove existing ballast, capacitor, and/or ignitor (where applicable) from fixture.


#### STEP 2


Rewire for line voltage to the lamp socket. Lamp is compatible with 120-277V from single phase, three phase wye, and three phase delta systems.

#### STEP 3

Install new LED replacement lamp. Ensure lamp is operating properly when power is turned on.











\*or other line for certain three phase systems such as 120/208 three phase wye systems

**EX39-based lamps** will work in both **E39** and **EX39** sockets.











# KT-LED36PSHID-EX39-8CSB-D HID REPLACEMENT LED LAMP

### PHYSICAL CHARACTERISTICS





#### **LAMP DIMENSIONS**

A (Body Length)	8.70"		
B (Illuminated Length)	3.87"		
C (Diameter)	3.30"		

BASE TYPE: EX39 (Mogul)

#### **ORDERING INFORMATION**

ORDER CODE		PACK QTY.	EASY CODE	UPC	
	KT-LED36PSHID-EX39-8CSB-D	16	ROL-76	843654128566	

### **CATALOG NUMBER BREAKDOWN**

## KT-LED36PSHID-EX39-8CSB-D

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Max Wattage
- 4 Power Select
- 5 Lamp Type
- 6 Base Type
- 7 80 CRI
- 8 Color Select
- 9 Color Select Designation
- 10 Direct Drive

- 9 Color Select Designation
  - 3000/4000/5000K