



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L620C Turnlok Conn 3W 20A 250V

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | L620C |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Locking Device Turnlock Connector, 20 A, 250 V Ac, 2 Poles, 3 Wires, Black/White, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 2.20 In;0.750 to 1.150 In (Cord) Diameter, 3.3 In Length, #18 to #8 Awg Wire Size, Impact Resistant, Corrosion Resistant, 0.37 LB |
| Weight per unit | 0.3720 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|---------|
| amperage rating | 20 |
| indoor/outdoor | Indoor |
| Poles | 2 |
| Voltage | 250.0 V |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|------------------------------------|
| Description | TURNLOK CONN 3W 20A 250V |
| extra long description | P&S L620C TURNLOK CONNECTOR 3W 20A |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007262018 |
| Manufacturers Part Number | L620C |
| UPC | 785007262018 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Industrial cord connectors |
| Type | CONNECTOR |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.372 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting
standard

Connector
CULUS, UL 498, FEDSPEC