# **LED Replacement Lamps**

LED R20/BR30/BR40 Reflector Lamps



Project Name	
	Type
Notes	

Current offers LED reflector lamps for all of your recessed can and downlighting application needs in the restaurant, hospitality and property management sectors.

## PERFORMANCE HIGHLIGHTS:

## **REFLECTOR LAMPS**

**Light Output Range:** 525-1070 Lumens

**CRI:** 80

**CCT:** 2700K, 3000K & 5000K

**Efficiency:** Up to 82 LPW **Wattage:** 7W, 10W & 13W

**Life:** 15,000-25,000 hours L70

**Temperature Rating:** -20°C to 40°C

Rating: Damp

**Dimmable:** Dims from 100% to 10%

### LIMITED WARRANTY

3 Years

## **FEATURES:**

- 15,000-25,000 hours rated life (L70)
- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

### **BENEFITS:**

### **Energy + Cost Savings**

- For example, using only 7 watts of energy, save over \$99 in energy costs over the rated life of a lamp versus a standard 45-watt incandescent lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources

## **LEARN MORE:**

To learn more about saving money and energy, go to www.gecurrent.com.

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.





## **LED Replacement Lamps**

LED R20/BR30/BR40 Reflector Lamps

Lnoc lable	
Spec Table	5
Spec rabic	

Project Name	
Date	Type
Notes	

Туре	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (ln)	Lumens Initial	Initial Color Temp	CRI I	Wattage Replacement	*Rated Life L70 (Hrs	) Dimmable		# Location Rating	Additional Information
								R20 RI	FLECT	OR L	AMPS					
	E26	7	38268	LED7DR20/827	120	6	3.64	525	2700	80	45	15,000	Yes	-	Damp	White
R20	E26	7	43233	LED7DR20/830	120	6	3.64	525	3000	80	45	15,000	Yes	-	Damp	White
	E26	7	38273	LED7DR20/850	120	6	3.64	525	5000	80	45	15,000	Yes	-	Damp	White
	BR30 REFLECTOR LAMPS															
	E26	10	68160	LED10DR303/827W	120	6	5.4	700	2700	80	65	25,000	Yes	*	Damp	Frosted, White body
	E26	10	68161	LED10DR303/830W	120	6	5.4	700	3000	80	65	25,000	Yes	*	Damp	Frosted, White body
BR30	E26	10	69107	LED10DR303/850W	120	6	5.4	700	5000	80	65	25,000	Yes	*	Damp	Frosted, White body
	E26	10	43234	LED10DR30V/827W	120	3	5.37	650	2700	80	65	15,000	Yes	-	Damp	Frosted, White body
	E26	10	43237	LED10DR30V/830W	120	3	5.37	650	3000	80	65	15,000	Yes	-	Damp	Frosted, White body
	BR40 REFLECTOR LAMPS															
	E26	13	64176	LED13DBR40/827	120	6	6.3	1070	2700	80	85	25,000	Yes	*	Damp	Frosted, White body
BR40	E26	13	14708	LED13DBR40/830	120	6	6.3	1070	3000	80	85	25,000	Yes	*	Damp	Frosted, White body
	E26	13	69108	LED13BR40/850	120	6	6.34	1070	5000	80	85	25,000	Yes	*	Damp	Frosted, White body

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

\* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

\*\* Minimum order quantity = 6

\*\* ENERGY STAR\* certified. Lamps without a "\*" are not ENERGY STAR\* certified.

# UL 1993 Environmental Requirements for LED LAMPS

Location, damp

- Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, damp

- Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet

Notes:

- Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.

