



# ESSENTIAL SERIES

## GENERAL PURPOSE LED BULBS

### KT-LED9.5A19-0-8XX-GU24

#### REPLACEMENT LAMP

#### DESCRIPTION

9.5W A19 Lamp | 2700–5000K | >80 CRI | Omni-Directional



<b>LAMP TYPE:</b> A19
<b>BASE TYPE:</b> GU24
<b>WATTAGE:</b> 9.5W
<b>COLOR TEMPERATURE:</b> 2700–5000K
<b>COLOR RENDERING INDEX (CRI):</b> >80
<b>WARRANTY:</b> 3 Years
<b>RATED LIFE:</b> L70 (15,000 Hours)



#### TYPICAL APPLICATIONS

- Table, desk, and floor lamps
- Wall sconces
- Surface-mount ceiling fixtures
- General lighting
- Pendant lights

#### PRODUCT FEATURES

- Energy efficient, 80%+ energy savings over legacy equivalents
- Lower heat generation than legacy equivalents
- Smooth, uniform dimming
- Smooth, diffused lens for comfortable glare-free performance
- Durable plastic housing lowers the risk for breakage
- Long life minimizes replacement and maintenance costs
- Suitable for use in damp locations
- PF >0.70
- Operating temperature range –4°F/–20°C to 95°F/35°C
- ANSI compliant construction ensures fitment for intended applications
- UL Listed
- UL enclosed rated, suitable for use in totally enclosed luminaires
- Meets Energy Star requirements
- Energy Star enclosed fixture rated
- Complies with Part 15 of FCC


#### ELECTRICAL AND PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED9.5A19-0-827-GU24	A19 bulb; Omni-directional; Dimmable	2700K	120V	9.5W	60W halogen	GU24	800 lm	>80	230°	Yes	84 lm/W
KT-LED9.5A19-0-830-GU24	A19 bulb; Standard flood; Dimmable	3000K	120V	9.5W	60W halogen	GU24	800 lm	>80	230°	Yes	84 lm/W
KT-LED9.5A19-0-840-GU24	A19 bulb; Standard flood; Dimmable	4000K	120V	9.5W	60W halogen	GU24	800 lm	>80	230°	Yes	84 lm/W
KT-LED9.5A19-0-850-GU24	A19 bulb; Standard flood; Dimmable	5000K	120V	9.5W	60W halogen	GU24	800 lm	>80	230°	Yes	84 lm/W

# KT-LED9.5A19-0-8XX-GU24

## REPLACEMENT LAMP

### PHYSICAL CHARACTERISTICS



### LAMP DIMENSIONS

A (Diameter)	2.36"
B (Length)	4.33"

BASE TYPE: GU24

### PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	15.55" × 13.07" × 10.55"
Carton Weight	11.4 lbs

### ORDERING INFORMATION

ORDER CODE	CARTON QUANTITY	ITEM STATUS	EASY CODE	UPC
KT-LED9.5A19-0-827-GU24	60 pcs	Active	XHC-49	843654126500
KT-LED9.5A19-0-830-GU24	60 pcs	Active	DUI-68	843654126517
KT-LED9.5A19-0-840-GU24	60 pcs	Active	QDB-97	843654126524
KT-LED9.5A19-0-850-GU24	60 pcs	Active	GVG-85	843654126531

### CATALOG NUMBER BREAKDOWN

# KT-LED9.5A19-0-8XX-GU24

1 2 3 4 5 6 7 8

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Shape
- 5 Omni-Directional
- 6 800 Series
- 7 Color Temperature
- 8 Base Type GU24