



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LB350DCG 3.5 Cond Body C/G

Appleton/Oz Gedney

Catalog Number	LB350DCG
Manufacturer	Appleton/Oz Gedney
Description	Emt Conduit Bodies, Aluminum Threaded For Rigid Conduit and Imc, Series: LB, Set Screw, Material: Conduit Body: Diecast, Copperfree Aluminum/Epoxy Powder Coat, Cover: Stamped Aluminum, Natural Finish, Gasket: Neoprene, UI Standard: 514A, Trade Size: 3-1/2
Weight per unit	10.0 (lbs/each)
Product Category	Alum

Material, Color, and Finish

Finish	Epoxy Powder Coat
--------	-------------------

Dimensions and Weight

Height	7.39
Hub Size	1-1/4
Length	7.7900000000000000
Width	2.7900000000000000

Descriptions

Description	3.5 COND BODY C/G
extra long description	EGS LB350DCG 3-1/2 THD ALUM LB BDY
Long Description	EMT Conduit Bodies, Aluminum Threaded for rigid conduit and IMC, Series: LB,Set Screw, Material: Conduit body: diecast, copperfree aluminum/epoxy powder coat, Cover: stamped aluminum, natural finish, Gasket: neoprene, UL Standard: 514A, Trade Size: 3-1/2
Product Type	3-1/2 THD Alum LB Bdy CVR GSKT
Special Features	3-1/2 IN Trade Size, Type LB Aluminum Threaded Conduit Body, Maximum No. of Conductors 3 - #350MCM, Volume 304.90 IN ³ , For Use With Rigid and IMC Conduit, Furnished With Cover and Gasket

Manufacturer Information

Brand	Appleton
GTIN	00687855001316
Manufacturers Part Number	LB350DCG
UPC	687855001316

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit Body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	10

Uses, Certifications, and Standards

Application	Provides access to the interior of the raceway for wire pulling , splicing and maintenance, Allows connection of straight and branch conduit runs and 90 degree bends
standard	CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E53330;UL Standard: 514A