

LED Replacement Lamps

A-Line Lamps



Project Name _____

Date _____ Type _____

Notes _____

Current offers dimmable LED A-Line lamps as excellent replacements for standard 25-watt, 40-watt, 60-watt, 75-watt and 100-watt incandescent lamps.

PERFORMANCE HIGHLIGHTS:

A-LINE LAMPS	
Light Output Range:	300-1600 Lumens
CRI:	80
CCT:	2700K, 3000K, 4000K & 5000K
Input Voltage:	120
Efficiency:	Up to 107 LPW
Wattage:	3.5W-19W
Life:	15,000 & 25,000 hours L70
Temperature Rating:	-20°C to 40°C
Rating:	Damp
Dimmable:	Dims from 100% to 10%

LIMITED WARRANTY

3 Years

FEATURES:

- Up to 25,000 hours rated life (L70)
- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

BENEFITS:

- **Energy + Cost Savings**
For example, a 100-watt incandescent replacement lamp using 13 watts of energy and producing 800 lumens can save over \$129 in energy costs over the rated life of the lamp versus a standard 840 lumen, 60-watt incandescent A19 based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent light sources

LEARN MORE:

To learn more about saving money and energy, go to www.gecurrent.com.

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

LED Replacement Lamps

A-Line Lamps

Spec Table

Project Name _____

Date _____ Type _____

Notes _____

Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	# Location Rating	Additional Information	
A-LINE LAMPS																
A-15	E26	3.5	23240	LED4DA15MAGC-2BT	120	6	3.5	300	2700	80	40	15,000	Yes	★	Damp	All Glass, Clear, 2 pack
	E26	4	34038	LED4DA15-W3/827	120	6	3.5	300	2700	80	40	15,000	Yes	-	Damp	White
	E26	4	25277	LED4DFA15-GW2	120	6	3.5	300	2700	80	40	15,000	Yes	-	Damp	All glass, White, 2 pack
	E26	5.5	25986	LED5DFA15-GW-2 120	120	6	3.5	500	2700	80	60	15,000	Yes	★	Damp	All Glass, Frosted, 2 pack
A-19	E26	4.5	37669	LED5DAGCSW-2P 120	120	6	4.4	450	2700	80	40	15,000	Yes	★	Damp	All Glass, Clear, 2 pack
	E26	6	69115	LED6DA19/827	120	6	4.4	480	2700	80	40	15,000	Yes	★	Damp	White, Omnidirectional
	E26	6	69118	LED6DA19/830	120	6	4.4	480	3000	80	40	15,000	Yes	★	Damp	White, Omnidirectional
	E26	6	69132	LED6DA19/840	120	6	4.4	480	4000	80	40	15,000	Yes	★	Damp	White, Omnidirectional
	E26	6	69144	LED6DA19/850	120	6	4.4	480	5000	80	40	15,000	Yes	★	Damp	White, Omnidirectional
	E26	7	37674	LED7DAGCSW-2P	120	6	4.4	800	2700	80	60	15,000	Yes	★	Damp	All Glass, Clear, 2 pack
	E26	8	99192	LED8AG/DL/4PK 120	120	6	4.4	760	5000	80	60	15,000	No	-	Damp	All Glass, Frosted, 4 pack
	E26	8	99190	LED8AG/SW/4PK 120	120	6	4.4	760	2700	80	60	15,000	No	-	Damp	All Glass, Frosted, 4 pack
	E26	10	69117	LED10DA19/827	120	6	4.4	800	2700	80	60	15,000	Yes	★	Damp	White, Omnidirectional
	E26	10	69119	LED10DA19/830	120	6	4.4	800	3000	80	60	15,000	Yes	★	Damp	White, Omnidirectional
	E26	10	69133	LED10DA19/840	120	6	4.4	800	4000	80	60	15,000	Yes	★	Damp	White, Omnidirectional
	E26	10	69146	LED10DA19/850	120	6	4.4	800	5000	80	60	15,000	Yes	★	Damp	White, Omnidirectional
	GU24	10	38220	LED10DA19GU24827	120	6	4.4	800	2700	80	60	15,000	Yes	★	Damp	White, Omnidirectional
	A-21	E26	12	76037	LED12DA21/827	120	6	5.16	1100	2700	80	75	15,000	Yes	★	Damp
E26		12	76041	LED12DA21/830	120	6	5.16	1100	3000	80	75	15,000	Yes	★	Damp	White, Omni, ES 2.0
E26		12	76045	LED12DA21/840	120	6	5.16	1100	4000	80	75	15,000	Yes	★	Damp	White, Omni, ES 2.0
E26		12	76102	LED12DA21/850	120	6	5.16	1100	5000	80	75	15,000	Yes	★	Damp	White, Omni, ES 2.0
E26		12	73404	LED12DA21/850FE	120	6	5.31	1100	5000	80	75	25,000	Yes	-	Enclosed	White, Enclosed, Omni
E26		12	73384	LED12DA21/830FE	120	6	5.31	1100	3000	80	75	25,000	Yes	-	Enclosed	White, Enclosed, Omni
E26		15	76038	LED15DA21/827	120	6	5.16	1600	2700	80	100	15,000	Yes	★	Damp	White, Omni, ES 2.0
E26		15	76043	LED15DA21/830	120	6	5.16	1600	3000	80	100	15,000	Yes	★	Damp	White, Omni, ES 2.0
E26		15	76060	LED15DA21/840	120	6	5.16	1600	4000	80	100	15,000	Yes	★	Damp	White, Omni, ES 2.0
E26		15	76117	LED15DA21/850	120	6	5.16	1600	5000	80	100	15,000	Yes	★	Damp	White, Omni, ES 2.0
GU24		15	46666	LED15DA21GU24827	120	6	5.43	1600	2700	80	100	15,000	Yes	-	Damp	White, Omnidirectional
E26		4/13/07	38188	LED13A30/100/827	120	6	5.31	400/1400/840	2700	80	30/70/100	15,000	-	-	Damp	White, 3-Way
E26		5/19/10	38563	LED19A50/150/827	120	6	5.31	650/2155/1300	2700	80	50/100/150	15,000	-	-	Damp	White, 3-Way

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a "★" are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.