



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED6A190830 6W Led A19 30K Dim 450LM 80cri

Keystone Technologies

| | |
|------------------|---|
| Catalog Number | LED6A190830 |
| Manufacturer | Keystone Technologies |
| Description | A19 Omni-Directional Bulb, 40W Equivalent, E26 Medium Base, 3000K, 80 Cri |
| Weight per unit | 0.1700 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|---------|
| Ballast Type | N/A |
| beam angle | 230 Deg |
| Circuit Type | N/A |
| Input Voltage | 120V |
| ip rating | N/A |
| lumens | 460 |
| Nominal Length | N/A |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Warranty | 3 |
| Wattage | 5.7 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | E26 |
| color rendering index (cri) | >80 Deg |
| color temperature | 3000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | N/A |
| Description | 6W LED A19 30K DIM 450LM 80CRI |
| extra long description | Key KT-LED6A19-O-830 /G2 40W Equiv. |
| Long Description | A19 Omni-Directional Bulb, 40W Equivalent, E26 Medium Base, 3000K, 80 CRI |
| Product Type | 40W Equiv., 6W, 450 Lumen, A19, E26, =80 Cri, Dimmable 27K/3 |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Keystone |
| GTIN | 00843654130156 |
| Manufacturers Part Number | KT-LED6A19-O-830 /G2 |
| UPC | 843654130156 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED A-LINE SHAPE LAMPS

Packaging

Carton 1

Package 5

Weight Per each 0.17

Uses, Certifications, and Standards

Energy Star Y