




GE  
Lighting

## 90102 - GE LED PAR20

### LED7DP202B830/20

 Energy-efficient LED lamps. Long life.

### Product Photo



#### GENERAL CHARACTERISTICS

Lamp Type	LED-PAR
Primary Application	Indoor Floodlight
Rated Life (Hours)	25000 h
Bulb Shape	PAR20

#### PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	3600 cd
Lumens per Watt (Efficacy)	73 lm
Nominal Initial Lumen per Watt	73
Rated Beam Spread	20 rad
Initial Lumens-nominal	520 lm
Color Rendering Index-CRI	83
Color Temperature	3000 K

#### PRODUCT INFORMATION

Product Code	90102
Description	LED7DP202B830/20
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168901024
Standard Package GTIN	00043168901024
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168901024
Alternative Unit Of Measure	CASE

#### ELECTRICAL CHARACTERISTICS


Voltage <Nom>	120 V
Rated power (Watts)	7 W



GE  
Lighting

## 90102 - GE LED PAR20

### LED7DP202B830/20

 Energy-efficient LED lamps. Long life.

### Product Photo



#### GENERAL CHARACTERISTICS

Lamp Type	LED-PAR
Primary Application	Indoor Floodlight
Rated Life (Hours)	25000 h
Bulb Shape	PAR20

#### PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	3600 cd
Lumens per Watt (Efficacy)	73 lm
Nominal Initial Lumen per Watt	73
Rated Beam Spread	20 rad
Initial Lumens-nominal	520 lm
Color Rendering Index-CRI	83
Color Temperature	3000 K

#### PRODUCT INFORMATION

Product Code	90102
Description	LED7DP202B830/20
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168901024
Standard Package GTIN	00043168901024
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168901024
Alternative Unit Of Measure	CASE

#### ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	7 W