



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LT121000 1/2" Met L/T, Non UI 1000' *Southwire Company*



Catalog Number	LT121000
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 1/2 In Trade Size, 0.82 to 0.84 In Conduit Outer Diameter, 0.622 to 0.642 In Conduit Inner Diameter, Titan(R) Ef Style, 1000 FT Length, Galvanized, Gray, 4 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 23 LB/100 FT
Weight per unit	0.2600 (lbs/ft)
Product Category	Liquid Tight Conduit

Features

outside diameter	844
------------------	-----

Descriptions

Description	1/2" MET L/T, NON UL 1000'
extra long description	SWC 55093802 Titan2 Type EF Extra-F

Manufacturer Information

GTIN	00032886042652
UPC	032886042652

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Packaging

Carton	1000
Weight Per foot	0.26