



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## LT2 2" Met L/T, Non UI 50' *Southwire Company*



Catalog Number	LT2
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 2 In Trade Size, 2.34 to 2.375 In Conduit Outer Diameter, 2.02 to 2.045 In Conduit Inner Diameter, Titan(R) Ef Style, 50 FT Length, Galvanized, Gray, 12 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 131 LB/100 FT
Weight per unit	1.1 (lbs/ft)
Product Category	Liquid Tight Conduit

### Features

outside diameter	2277
------------------	------

### Descriptions

Description	2" MET L/T, NON UL 50'
extra long description	SWC 55107202 Titan2 Type EF Extra-F

### Manufacturer Information

GTIN	00032886043109
UPC	032886043109

### Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

### Packaging

Carton	50
Weight Per foot	1.1