



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832



## LL29 3/4" Alu LL MK9 Conduit Body

*Crouse-Hinds*

Catalog Number	LL29
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Mark 9 Conduit Outlet Body, Copper-Free Aluminum, LL Shape, 3/4"
Weight per unit	0.5200 (lbs/each)
Product Category	Alum

### Features

dimensions	5.2500 IN X 1.6300 IN X 2.3100 IN
------------	-----------------------------------

### Material, Color, and Finish

Finish	Untreated
--------	-----------

### Dimensions and Weight

Height	1-5/8
Hub Size	3/4 in
Length	5-1/4
Width	2-3/8

### Descriptions

Description	3/4" ALU LL MK9 CONDUIT BODY
extra long description	CRS-H LL29 3/4 LL MARK 9 CNDT BODY
Features	Mark 9 copper-free aluminum conduit bodies, covers and gaskets from Eaton's Crouse-Hinds Division are used in conduit systems to act as pull outlets for conductors being installed, provide openings for making splices and taps in conductors, make 90 degree bends in conduit runs, and provide for access to conductors for maintenance and future system changes. Mark 9 bodies are offered in seven different shapes, and they provide more room for heavier conductors.
Long Description	Eaton Crouse-Hinds series Condulet Mark 9 conduit outlet body, Copper-free aluminum, LL shape, 3/4"
Product Type	3/4 LL Mark 9 CNDT Body

### Manufacturer Information

Brand	Eaton
GTIN	00782274524306
Manufacturers Part Number	LL29
UPC	782274524306

### Taxonomies, Classifications, and Categories

Category Description	Form 9 condulets, covers & gaskets
Type	Conduit outlet body



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832

## Packaging

Carton	1
Package	5
Weight Per each	0.52

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D