



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LT50 1/2" LT STR Steel Conn *Crouse-Hinds*

|                  |  |
|------------------|--|
| Catalog Number   | LT50   |
| Manufacturer     | Crouse-Hinds   |
| Description      | Liquid Tight Straight Connector, 1/2 In Trade Size, Malleable Iron (Body, Gland Nut);Steel (Ferrule, Lock Nut);Polyethylene (Sealing Ring);Thermoplastic Elastomer (Sealing Gasket) Material, Zinc Electroplated, 1.250 In Length, 1.250 In Diameter, Non-Insulated, Threaded Connection, 0.22 LB/Ea |
| Weight per unit  | 0.2200 (lbs/each)  |
| Product Category | Liquid Tight Fittings  |

### Features

|                   |                                   |
|-------------------|-----------------------------------|
| connection        | Threaded                          |
| dimensions        | 1.7500 IN X 1.2500 IN X 1.2500 IN |
| installation type | THREADED                          |

### Material, Color, and Finish

|       |                |
|-------|----------------|
| Color | MALLEABLE IRON |
|-------|----------------|

### Descriptions

|                        |                          |
|------------------------|--------------------------|
| Description            | 1/2" LT STR STEEL CONN   |
| extra long description | MIDWEST LT50 1/2 LT CONN |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Eaton          |
| GTIN  | 00784564300508 |
| UPC   | 784564300508   |

### Taxonomies, Classifications, and Categories

|                      |                       |
|----------------------|-----------------------|
| Category Description | METALLIC FITTINGS     |
| Type                 | Liquidtight connector |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 25   |
| Package         | 100  |
| Weight Per each | 0.22 |

### Uses, Certifications, and Standards

|          |                              |
|----------|------------------------------|
| standard | UL 467, UL 514B, CSA C22.121 |
|----------|------------------------------|