



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LPCC20 20A 600V TD Class CC Low Peak Fuse

*Bussmann Fuses*

Catalog Number	LPCC20
Manufacturer	Bussmann Fuses
Description	Low Peak Fuse, Time Delay Fuse Speed, Class CC Fuse, 12 S @ 200% Response Time, 20 A, 600 V Ac;300 V DC, Melamine Tube Material, Dual Element, 0.41 In Diameter, 1.5 IN38.1 MM Overall Length, 0.02 LB
Weight per unit	0.0200 (lbs/each)
Product Category	Current Limiting

### Features

amperage rating	20
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
element	Dual
media	Yes

### Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

### Descriptions

Description	20A 600V TD CLASS CC LOW PEAK FUSE
extra long description	BUSS LP-CC-20 LOW PEAK CC TIME DELA
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Special Features	Rejection Style

### Manufacturer Information

Brand	Eaton
GTIN	00051712180276
UPC	051712180276

### Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	10
Weight Per each	0.02

## Uses, Certifications, and Standards

standard	CSA Certified ,UL Listed,RoHS Compliant,CE Marked
----------	---