



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 North East 20th Ave.  
76067-0000, TX Mineral Wells  
Phone: 940-325-5503  
Fax: 940-325-5544



## LT250 2-1/2" LT STR Steel Conn

*Crouse-Hinds*

|                  |  |
|------------------|--|
| Catalog Number   | LT250  |
| Manufacturer     | Crouse-Hinds   |
| Description      | Liquid Tight Straight Connector, 2-1/2 In Trade Size, Malleable Iron (Body, Gland Nut);Steel (Ferrule, Lock Nut);Polyethylene (Sealing Ring);Thermoplastic Elastomer (Sealing Gasket) Material, Zinc Electroplated, 2.188 In Length, 4 In Diameter, Non-Insulated, Threaded Connection, 363.8 LB/100 |
| Weight per unit  | 2.9 (lbs/each)   |
| Product Category | Liquid Tight Fittings  |

### Features

|                   |                                   |
|-------------------|-----------------------------------|
| connection        | Threaded                          |
| dimensions        | 3.1900 IN X 4.0000 IN X 4.0000 IN |
| installation type | THREADED                          |

### Material, Color, and Finish

|       |                |
|-------|----------------|
| Color | MALLEABLE IRON |
|-------|----------------|

### Descriptions

|                        |                             |
|------------------------|-----------------------------|
| Description            | 2-1/2" LT STR STEEL CONN    |
| extra long description | MIDWEST LT250 2 1/2 LT CONN |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Eaton          |
| GTIN  | 00784564302502 |
| UPC   | 784564302502   |

### Taxonomies, Classifications, and Categories

|                      |                       |
|----------------------|-----------------------|
| Category Description | METALLIC FITTINGS     |
| Type                 | Liquidtight connector |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 5   |
| Weight Per each | 2.9 |

### Uses, Certifications, and Standards

|          |                            |
|----------|----------------------------|
| standard | UL 467, UL 514B, CSA C22.2 |
|----------|----------------------------|