



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LT38 3/8" Met L/T, Non UI 100' *Southwire Company*



| | |
|------------------|--|
| Catalog Number | LT38 |
| Manufacturer | Southwire Company |
| Description | Liquidtight Flexible Conduit, 3/8 In Trade Size, 0.69 to 0.71 In Conduit Outer Diameter, 0.484 to 0.504 In Conduit Inner Diameter, Titan(R) Ef Style, 100 FT Length, Galvanized, Gray, 4 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 22 LB/100 FT |
| Weight per unit | 0.2200 (lbs/ft) |
| Product Category | Liquid Tight Conduit |

Features

| | |
|------------------|-----|
| outside diameter | 700 |
|------------------|-----|

Dimensions and Weight

| | |
|----------|------|
| Diameter | 3/8" |
|----------|------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 3/8" MET L/T, NON UL 100' |
| extra long description | SWC 55093703 Titan2 Type EF Extra-F |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00032886042683 |
| UPC | 032886042683 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | Liquid Tight |
|----------------------|--------------|

Packaging

| | |
|-----------------|------|
| Carton | 100 |
| Weight Per foot | 0.22 |