



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725



M21375499 Multi-Purpose Nylon Labels W/Ribbon, 0.375"

Brady Worldwide, Inc.

Catalog Number	M21375499
Manufacturer	Brady Worldwide, Inc.
Description	Aggressive Adhesive Multi-Purpose Nylon Labels With Ribbon For M210 M211 BMP21-Plus Printers - 0.375"
Weight per unit	0.1650 (lbs/each)
Product Category	Markers & Marking Tapes

Features

included	1 Continuous Roll (16 Feet)
labels per package	Cartridge of 16 Feet
Material	Nylon Cloth
Temperature Range	-40 °F - 194 °F

Material, Color, and Finish

Color	Black on White
Finish	Matte

Dimensions and Weight

Length	16
Size	0.375 in W x 16 ft L
Thickness	0.0065
Width	0.375

Descriptions

Description	MULTI-PURPOSE NYLON LABELS W/RIBBON, 0.375"
extra long description	BRADY M21-375-499 Label Nylon 0.375
Features	High adhesion and high pliability are the hallmarks of Brady's nylon cloth (B-499) label material designed to meet a broad array of identification requirements from control panels to liquid nitrogen environments.
Long Description	Aggressive Adhesive Multi-Purpose Nylon Labels with Ribbon for M210 M211 BMP21-PLUS Printers - 0.375"
Product Type	Label Nylon 0.375IN X 16FT BK/WT
Special Features	Aggressive Adhesive;Low Temperature;Permanent Adhesive

Manufacturer Information

Brand	Brady®
GTIN	00662820899631
Manufacturers Part Number	M21-375-499
UPC	662820899631



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725

Taxonomies, Classifications, and Categories

Category Description	Printers and Labeling
Type	Label

Packaging

Carton	1
Weight Per each	0.165

Uses, Certifications, and Standards

Application	Component and Equipment Labeling;Data and Telecommunications Labeling;Electrical Labeling;General Identification;Wire and Cable Labeling
standard	Halogen Free (DIN VDE 0472 Part 815)