

# Eaton MMX11AA2D8N0-0

Catalog Number: MMX11AA2D8N0-0

Eaton M-Max Series Adjustable Frequency AC Drives Basic Controller, Full version, AA software design series, FS2 frame, 100-120V, 230V, IP20 enclosure rating, 0.75 hp, 2.8A output, 12.4A input, Single-phase in, three-phase out

## General specifications



Photo is representative

### Product Name

Eaton M-Max Series sensorless vector adjustable frequency drive

### Catalog Number

MMX11AA2D8N0-0

### UPC

786685268460

### Product Length/Depth

3.54 in

### Product Height

4 in

### Product Width

7.68 in

### Product Weight

1.54 lb

### Warranty

2 year

### Compliances

RoHS Compliant

CE Marked

EMC Category C2, C3, and C4 (Level H): With an internal RFI filter option

C-Tick Compliant

### Certifications

EN 60204-1

EN 61800-5-1

UL Listed

EN 61800-3

cUL Certified

### Catalog Notes

Horsepower ratings are based on the use of a 240V, 460V, and 575V NEMA B, four- or six-pole squirrel cage induction motor and are for reference only.

## defaultTaxonomyAttributeLabel

### Horsepower

0.75 hp

### Phase

Single-phase in, three-phase out

### Special features

AA software design series

### Type

Full version

### Voltage rating

100-120 V, 230 V

### Frame size

2

### Rating

IP20

### Input current

12.4 A

### Output current - max

2.8 A

## Resources

### Brochures

[Variable frequency drive - Product overview](#)

[M-Max Series adjustable frequency drives](#)

### Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

### Drawings

[MMX\\_\(FR2\) 3D Model Xchange](#)

[MMX\\_\(FR2\) 2D Drawing Xchange](#)

[MMX\\_\(FR2\) 2D PDF](#)

[MMX\\_\(FR2\) AutoCAD 2D Footprint](#)

[MMX\\_\(FR2\) 3D Inventor](#)

[MMX\\_\(FR2\) AutoCAD 2D Footprint \(mm\)](#)

### Installation instructions

[User Manual, M-Max Series Adjustable Frequency Drive](#)

### Specifications and datasheets

[Eaton Specification Sheet - MMX11AA2D8N0-0](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)