

Eaton MMX32AA7D0N0-0

Catalog Number: MMX32AA7D0N0-0

Eaton M-Max Series sensorless vector adjustable frequency drive, Three-phase in, three-phase out, 7.0A, 2.0HP, 230V input and output voltage, FS2, W/O EMC



Photo is representative

General specifications

Product Name	Catalog Number
Eaton M-Max Series sensorless vector adjustable frequency drive	MMX32AA7D0N0-0
	UPC
	786685268750
Product Length/Depth	Product Height
5.5 in	4.5 in
Product Width	Product Weight
3 in	1.5 lb
Compliances	
CE Marked	
RoHS Compliant	
C-Tick Compliant	

defaultTaxonomyAttributeLabel

Amperage Rating

7A

Horsepower

2 hp

Phase

Three-phase in, three-phase out

Input voltage

230 V

Output voltage - max

230 V

Output voltage - min

230 V

Resources

Brochures

[Variable frequency drive - Product overview](#)

[M-Max Series adjustable frequency drives](#)

Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

Drawings

[MMX_\(FR2\) 3D Inventor](#)

[MMX_\(FR2\) 2D PDF](#)

[MMX_\(FR2\) 2D Drawing Xchange](#)

[MMX_\(FR2\) 3D Model Xchange](#)

[MMX_\(FR2\) AutoCAD 2D Footprint](#)

[MMX_\(FR2\) AutoCAD 2D Footprint \(mm\)](#)

Installation instructions

[User Manual, M-Max Series Adjustable Frequency Drive](#)

Specifications and datasheets

[Eaton Specification Sheet - MMX32AA7D0N0-0](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)