



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MMX34AA023F00 Mmax 3P 480V In/3P 480V Out 23A 15HP FS4 W Emc & 5 *Eaton Corp*

Catalog Number	MMX34AA023F00
Manufacturer	Eaton Corp
Description	Eaton M-Max Series Adjustable Frequency Drive Full Version AA Software Design Series FS4 Frame 380–480V 3-Phase In 460V Three-Phase Out IP20 Enclosure Rating 15 HP 23A Output Current 23A Nominal AC Current
Weight per unit	12.5 (lbs/each)
Product Category	Ac Drives

Features

dimensions	6.5000 IN X 6.6100 IN X 14.5700 IN
Number of Phases	Three-phase

Descriptions

Description	MMAX 3P 480V IN/3P 480V OUT 23A 15HP FS4 W EMC & 5
extra long description	ETN MMX34AA023F0-0 MMX 480V 23A, 15H
Features	Demand more simplicity. The M-Max series of variable frequency drive is a compact system with a broad power range. Factor in the conformal board coating, unique mounting characteristics, simple programming, and its 50°C Rating and the M-Max is perfectly suited for machinery applications in many industries including material handling, HVAC, pumping and more.
Long Description	Eaton M-Max Series Adjustable Frequency Drive Full version AA software design series FS4 frame 380–480V 3-phase in 460V three-phase out IP20 enclosure rating 15 hp 23A Output current 23A Nominal AC current
Product Type	MMX 480V 23A, 15HP, FS4, W Emc&5% Choke

Manufacturer Information

Brand	Eaton
GTIN	00786685626666
Manufacturers Part Number	MMX34AA023F00
UPC	786685626666

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Sensorless vector adjustable frequency drive

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	12.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & EOEM - Electrical Assemblies and
EOEMs - Other

standard

EN 61800-3,EN 61800-5-1,EN 60204-1,IEC Rated,cUL Listed,UL
Listed,RoHS Compliant,EMC Category C2, C3, and C4 (Level H):
With an internal RFI filter option,C-Tick Compliant,CE Marked