



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MSZ101WH Maestro DV 8A 0-10V Occupancy White

Lutron

Catalog Number	MSZ101WH
Manufacturer	Lutron
Description	Maestro 0-10V Dimmer Occupancy/Vacancy Sensor, Passive Infrared, 8A Fluorescent Ballast or Led Driver, 120-277V, In White
Weight per unit	0.3000 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

body	Plastic
load	8 A/0-10VDC
media	Yes
sensing range	900 ft2 (82 m2) major motion coverage/400 ft2 (36 m2) minor motion coverage
supply voltage	120 to 277

Descriptions

Description	MAESTRO DV 8A 0-10V OCCUPANCY WHITE
extra long description	LUT MS-Z101-WH 0-10V DIMMER SENSOR
Long Description	Maestro 0-10V dimmer occupancy/vacancy sensor, passive infrared, 8A fluorescent ballast or LED driver, 120-277V, in white
Product Type	0-10V Dimmer Sensor White
Special Features	Passive infrared sensors that automatically control the lights in an area. These sensors detect heat from occupants moving within an area to determine when the space is occupied. Combines a Maestro 0-10 V dimmer with an occupancy sensor. Controls 1-10 VDC electronic fluorescent ballast or LED driver load types. Passive infrared motion detection with exclusive Lutron XCT Technology for fine motion detection. 180 degree sensor field-of-view. Up to 30 ft x 30 ft (9 m x 9 m) [900 ft2 (81 m2)] major motion co

Manufacturer Information

Brand	Lutron
GTIN	00784276099844
Manufacturers Part Number	MS-Z101-WH
UPC	784276099844

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Occupancy/Vacancy sensor dimmer, multi-location/3-way/single-pole, 0-10 V



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, cUL, Title 20/24 certified